








Characteristics

General Characteristics	Standard	Value
number of contact inserts		2
flammability	UL 94	V-0
Electrical Characteristics	Standard	Value
insulation resistance	IEC 60512-3-1	$\geq 10^{10} \Omega$
Climatical Characteristics	Standard	Value
climatic category	IEC 60068-1	40 / 125 / 10
upper temperature	IEC 60512-11-9	+125 °C
lower temperature	IEC 60512-11-10	-40 °C
Mechanical Characteristics	Standard	Value
mechanical operation	IEC 60512-9-1	≥ 500 mating cycles/ ≥ 2000 mating cycles with special contact plating
Materials	Standard	Value
pin module		PA-GF
color		black

Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during
practical usage of the product. Any product information is for descriptive usage only and not legally binding;
particularly the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or
"Haltbarkeitsgarantie").

Gewicht (errechnet) / Calc WT: 14,3 g				Zul. Abw./Tolerances: ISO 2768-m		 DIN / ISO 13715	Maßstab / Scale : 2:1 (1:1)		A3		
Prüfmaß / Testdimension							CUSTOMER DRAWING				
Teileindex / Partindexnumber:				Buchsenmodul <i>socket module</i>							
Bagatelle change:											
				Gez.	09.10.2015						
				Drawn	PWOELFFLE						
				Status	Released						
				Gepr.	08.09.2017						
				Checked	MGRIMM	M C146 10B002 800 15					
04	201700257	30.08.2017	PWÖLF	Amphenol Tuchel Industrial GmbH							
03	201600736	27.10.2016	PWÖLF								
02	201600135	01.03.2016	PWÖLF								
01	201500704	09.10.2015	PWÖLF								
Index	Änderung / Description	Datum / Date	Name	Ers. f. / Replacement for : M-C146 10B002 900 15 Rev.01							