

VT SF 00/21 MC NE BL V0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 1 - 1.3 mm, 21 x 3.2 mm, blue
Order No.	1730580002
Type	VT SF 00/21 MC NE BL V0
GTIN (EAN)	4008190954475
Qty.	800 pc(s).
compatible printer	2438520000 2438510000
Alternative product	1918530000

VT SF 00/21 MC NE BL V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3.2 mm	Depth (inches)	0.126 inch
Height	21 mm	Height (inches)	0.827 inch
Net weight	0.236 g	Width	3.2 mm
Width (inches)	0.126 inch		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

General data

Colour	blue	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Conductor and cable markers
Operating temperature range	-50...120 °C	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Recommended industries	Transportation, Machinery
Size of labelling field	21 x 3.2 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Width	3.2 mm

Conductor and cable markers

Conductor O.D.	1 - 1.3 mm	Conductor O.D., max.	1.3 mm
Conductor O.D., min.	1 mm	Conductor cross-section, max.	0.25 mm ²
Conductor cross-section, min.	0.18 mm ²	Cross-section for connected wire	0.18 - 0.25 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S

VT SF 00/21 MC NE BL V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

