





D

C

B

A


Link: S:\DZIAL_BADAN_LI_ROZWOJU\PUBLICZNY_PROJEKTY_DPP\TIME\1S1P_CGA103450A - 823\1S1P_CGA103450A - 823 [TME]_3.6V



Specifications

Nominal Voltage [v]		3.6
Minimum Capacity [mah]		1850
Typical Capacity [mah]		1950
Charging Voltage [v]		4.2
Size [mm]		wg. rysunku
Weight [g]		50
Typical Charge [mA]		370
Rapid Charge [mA]		1295
max. Continuous discharge current [mA]		2000
Charge temperature	Typical	0C -45C
	Rapid	10C - 45C
Discharge temperature	Continuous	-20C- 60C
Storage temperature	Recommended	-20C - 35C

LABEL: 45 x 25 mm



Materiał:		Powloka:		Odbiorca:	Skala:	Wersja:	Rewizja:
				TME	1:1	A	0
Konstruował:	Konstruktor mechanik					Arkusz:	1
Sprawdził:	Konstruktor elektryk					Arkuszy:	2
Zatwierdził:	Dyrektor techniczny					Masa:	
Technologicznie:	Główny technolog					Uwagi:	
Zgodność z wyt.:	Handlowiec						
Aktualizował:	Data aktualizacji:	Data wykonania:	Format arkusza:	Nazwa:		Nr rysunku:	
J. Dadacz	2020-11-06	2012-10-19	A4	1S1P CGA103450A - 823 CGA103450/1S1P		823-00-00	
Nietolerowane wymiary wykonywać wg PN-78/M-02139 szereg 13				Tolerancja kształtu i położenia wg PN-80/m-02138 szereg 13			

D

C

B

A