


BiTLAN U/UTP cat.6 LSOH B2ca

350MHz

Halogen-free, data transmission cable



BITNER BiTLAN U/UTP cat.6 LSOH B2ca



internal application



EN 60332-1



data transmission



halogen-free
EN 60754



low smoke emission
EN 61034



B2ca-s1a,d1,a1

Technical data:

Temperature range:

Operating temperature: -30°C to +70°C

Min. installation temp: -10°C

Bending radius:

during operation: $\geq 6 \times O.D.$

during installation: $\geq 8 \times O.D.$

Conductor diameter: $0,54 \pm 0,015 \text{ mm}$

Insulated core diameter: $0,985 \pm 0,05 \text{ mm}$

DC loop resistance at 20°C (max): $165 \Omega/\text{km}$

Insulation resistance (min): $5 \text{ G}\Omega \times \text{km}$

Resistance unbalance within a pair: $\leq 2\%$

Mutual capacitance at 1 kHz: $50 \pm 5 \text{ nF/km}$

Capacitance unbalance pair to ground at 1 kHz (max): 1600 pF/km

Nominal voltage: 150V

Test voltage - 1min:

AC 50 Hz: 700V

DC: 1000V

Characteristic impedance at 100MHz:

$100 \pm 5 \Omega$

NVP value: 67%

Return loss dB (min):

$f = 4\text{--}10 \text{ MHz: } 20 + 5 \times \log_{10}(f)$

$f = 10\text{--}20 \text{ MHz: } 25$

$f = 20\text{--}350 \text{ MHz: } 25 - 7 \times \log_{10}(f/20)$

Construction:

Conductors: solid round copper conductors

Insulation: special polyolefin compound

Core identification: wh/bu-bu, wh/or-or, wh/gn-gn, wh/bn-bn

Core arrangement: cores twisted in pairs, pairs twisted together with a circular filling element

Outer sheath: special LSOH compound

Outer sheath colour: orange RAL 2003, others colours available on customer's request

Marking: BITNER BiTLAN U/UTP 4x2x23AWG(0,54) cat.6 350MHz LSOH B2ca
EN 50173-1 ISO/IEC 11801 ANSI/TIA 568-C.2 ID no. CE RoHS
www.bitner.com.pl meters

Application:

BiTLAN U/UTP cat. 6 LSOH B2ca cables are applicable to computer networks with operating frequency band up to 350MHz. Suitable for transmission of data, audio and video signals with bitrate up to 1Gb/s. Dedicated for fixed installations within indoor structured cabling systems as per EN 50173-1, ISO/IEC 11801, ANSI/TIA 568-C.2 standards, as well as within industrial networks not exposed to external electromagnetic interferences.

Cables with flame retardant LSOH outer sheath ensuring low smoke emission acc. to EN 50268-2, IEC 61034-1(2) and limited emission of corrosive gases acc. to EN 50267, IEC 60754-2 should be installed in places with increased fire safety requirements.

Cables classified according to **EN 50575 (CPR)**.

Packaging:



Box
(305m)




Pallet 9150m
(30x305m)



Spool/Coil
500m



Spool/drum
1000m



Cu conductors

Circular filling element

PE insulation

LSOH outer sheath

Cat. no.	Construction	Cu wire	O.D. [mm]	CPR classification EN 50575	Cu [kg/km]	Cable weight [kg/km]	Bandwidth [MHz]
TI0119	U/UTP cat.6 LSOH B2ca	23AWG(0,54)	6,1	B2ca-s1a,d1,a1	19	47	350

Cable Factory BITNER reserves the right to modify the specifications without prior notice

BiTLAN U/UTP cat.6 LSOH B2ca

350MHz

Halogen-free, data transmission cable

Requirements of teletransmission data:

Frequency MHz	1	4	10	16	20	30	45	60	80	100	120	150	180	200	220	250	280	300	320	350
Attenuation ≤ dB/100m	2,1	3,8	6,0	7,6	8,5	10,5	13,0	15,1	17,7	19,9	22,0	24,8	27,5	29,1	30,7	33,0	35,2	36,6	38,0	40,0
NEXT ≥ dB	66,0	65,3	59,3	56,2	54,8	52,1	49,5	47,6	45,8	44,3	43,1	41,7	40,5	39,8	39,2	38,3	37,6	37,1	36,7	36,1
PS NEXT ≥ dB	64,0	63,3	57,3	54,2	52,8	50,1	47,5	45,6	43,8	42,3	41,1	39,7	38,5	37,8	37,2	36,3	35,6	35,1	34,7	34,1
ELFEXT ≥ dB/100m	66,0	58,0	50,0	45,9	44,0	40,5	36,9	34,5	32,0	30,0	28,4	26,5	24,9	24,0	23,1	22,0	21,0	20,5	19,9	19,1
PS ELFEXT ≥ dB/100m	64,0	55,0	47,0	42,9	41,0	37,5	33,9	31,4	28,9	27,0	25,4	23,5	21,9	21,0	20,1	19,0	18,0	17,5	16,9	16,1
RL ≥ dB	20,0	23,0	25,0	25,0	25,0	23,8	22,5	21,7	20,8	20,1	19,5	18,9	18,3	18,0	17,7	17,3	17,0	16,8	16,6	16,3

Transmission parameters graphs - examples of measurement results

