



Heat shrinkable tubing 2:1 - Halogen free

TL27

TL27 has a low shrink temperature which offers very fast recovery. Application fields include covering of heat sensitive parts, mechanical protection and cosmetic covering.

Features and benefits

- Very low shrink temperature
- Fast shrinking
- Halogen free



TL27 – a very flexible tubing for automotive applications or applications where halogens cannot be accepted.

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	2:1
Operating Temperature	-55 °C to +135 °C
Min. Shrink Temperature	+90 °C
Longitudinal change after shrinkage	+5 %/-15 %
Dielectric Strength	>20 kV/mm
Flammability	FMVSS 302



Heat Shrinkable Tubing 2:1



TYPE	Supplied Ø D min.	Size (imperial)	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Tools	Article-No.
TL27-1.2/0.6	1.2	3/64 "	0.6	0.31	500 m	Black (BK)	30-32	302-20120
TL27-1.6/0.8	1.6	1/16 "	0.8	0.33	500 m	Black (BK)	30-32	302-20160
TL27-2.4/1.2	2.4	3/32 "	1.2	0.36	500 m	Black (BK)	30-32	302-30240
TL27-3.2/1.6	3.2	1/8 "	1.6	0.39	300 m	Black (BK)	30-32	302-30320
TL27-4.8/2.4	4.8	3/16 "	2.4	0.42	150 m	Black (BK)	30-32	302-30480
TL27-6.4/3.2	6.4	1/4 "	3.2	0.45	100 m	Black (BK)	30-32	302-30640
TL27-9.5/4.8	9.5	3/8 "	4.8	0.48	100 m	Black (BK)	30-32	302-30950
TL27-12.7/6.4	12.7	1/2 "	6.4	0.52	100 m	Black (BK)	30-32	302-21270
TL27-19.1/9.5	19.1	3/4 "	9.5	0.58	100 m	Black (BK)	30-32	302-31900
TL27-25.4/12.7	25.4	1 "	12.7	0.67	100 m	Black (BK)	30-32	302-32540
TL27-38.1/19.1	38.1	1-1/2 "	19.1	0.76	100 m	Black (BK)	30-32	302-23810
TL27-50.8/25.4	50.8	2 "	25.4	0.85	100 m	Black (BK)	30-32	302-25080

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.

Recommended Tools			
	30	31	32
	H5002	H5004	E4500
	568	568	567

For more information on toolings please refer to the Application Tooling chapter.