


Data sheet Product LA 28 300 24



Cooling aggregates>Cooling aggregates with axial fan
 66 x 65 mm, with axial fan



High performance cooling aggregate

- compact construction by means of connected extruded profiles
- excellent efficiency by means of flow-optimised hollow fin structure
- powerful axial fans
- double-sided precise milled semiconductor mounting surfaces
- different width dimensions, customised machinings, surfaces, fan types and fan voltages upon request

Features

width:	65 mm
height:	65 mm
length:	300 mm
thermal resistance:	0.088 - 0.187 K/W
surface:	raw degreased aluminium (by the metre raw aluminium)
operating voltage of the fan motor:	• 12 V DC • 24 V DC • 48 V DC

Technical Drawing



Fan

ebmpapst 612 JH, 12 V DC

type:	ebmpapst 612 JH
dimensions:	60x60x32 mm
tension:	12 V DC
power inout:	7.7 W
max. air volume:	70 m ³ /h
temperature range:	-20°C... +70°C
speed:	11,700 min ⁻¹
noise level:	53 dB(A)
weight:	100 g
failure rate (L ₁₀):	L ₁₀ < 57,500 h (40°C)

ebmpapst 614 J/2HHP, 24 V DC

type:	ebmpapst 614 J/2HHP
dimensions:	60x60x32 mm
tension:	24 V DC
power inout:	14.6 W
max. air volume:	82 m ³ /h
temperature range:	-20°C... 75°C
speed:	15,000 min ⁻¹
noise level:	62 dB(A)
weight:	100 g
failure rate (L ₁₀):	L ₁₀ > 65,000 h (40°C)

ebmpapst 618 J/2HHP, 48 V DC

type:	ebmpapst 618 J/2HHP
dimensions:	60x60x32 mm
tension:	48 V DC
power inout:	14.6 W
max. air volume:	82 m ³ /h
temperature range:	-20°C... 75°C

speed:	15,000 min⁻¹
noise level:	62 dB(A)
weight:	100 g
failure rate (L ₁₀):	L₁₀ > 65,000 h (40°C)

Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
58511 Lüdenscheid

Telefon +49 2351 435-0
Telefax +49 2351 45754

info@fischerelektronik.de
www.fischerelektronik.de