


Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	03					
		See ECN 012244	A.A.C.	12/13/12	K.A.C.	12/13/12



PRODUCT CODE DESCRIPTION


RT50S
 COLOR
 (CONSULT FACTORY FOR AVAILABLE COLORS)

03

Type	Cable Range (mm)	Material	A	B	D	E	G	H	Min Loop Tensile Strength (newtons)
RT50S_	1.5 to 35	PA66	1.2 ±0.2	4.6±0.2	5.7 ±0.5	8.0 ±0.5	160.0 ±12.0	7.0 ±0.5	225

SEE CHART
Material
Dimension tolerances unless otherwise specified .XXXX = .XXX = .XX = .X = NOTED < =
Dimension Units mm
PERFORMANCE SPECIFICATION

ACAD MECH
2013



Drawn
Approved

G.G.G.
K.A.C.

10/8/91
10/01/10

Scale
Title

2:1

Computer File Number
CT\CST\2050012_03

ALL PROPRIETARY RIGHTS IN THE
SUBJECT MATTER SHOWN ON THIS
DRAWING ARE EXCLUSIVE
PROPERTY OF HELLERMANNTYTON

HellermannTyton®

7930 N. Faulkner Rd.
Milwaukee, WI 53224
Ph: (414) 355-1130
Fx: (414) 362-8338

**RT50S
RELEASABLE TIE**

Drawing—No

CT2050012CST

Format

AH

Sheet 1 of 1