










Part No.	Number of contacts	Code No.	A	B	C	D
DF13E-10DP-1.25V(65)	10	CL536-0566-0-65	12.1	5.0	7.5	8.7
DF13E-20DP-1.25V(65)	20	CL536-0567-0-65	18.35	11.25	13.75	14.95
DF13E-30DP-1.25V(65)	30	CL536-0568-0-65	24.60	17.50	20.00	21.20
DF13E-40DP-1.25V(65)	40	CL536-0569-0-65	30.85	23.75	26.25	27.45



Notes 1 : Lead co-planality include reinforced metal fittings shall be 0.1mm MAX.
2 : If there are pattern and a bia hole on  part, there is a possibility that it will make contact with the leads.

2	Brass	Contact area:Gold plated 0.2μm MIN Lead area:Tin plated 1μm MIN Under plating:Nickel 1μm MIN	5	Elastomer	Gray
			4	R. PVC	Electrostatic protection. Clear
1	Polyamide	Beige. UL94V-0	3	Phosphor bronze	Tin plated 1μm MIN
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 5 : 1	COUNT	DESCRIPTION OF REVISIONS	
DESIGNED		CHECKED		DATE	
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA 20200330		DRAWING NO. EDC-367983-65-00	
		CHECKED : TS. KUMAZAWA 20200330		PART NO. DF13E- * DP-1.25V(65)	
		DESIGNED : HK. HAYASHI 20200330		CODE NO. CL536-	
		DRAWN : DS. HIROWATARI 20200326			

