








Part No.	Number of contacts	Code No.	A	B	C
DF13EA-10DP-1.25V(65)	10	CL536-0570-0-65	12.1	5.0	8.7
DF13EA-20DP-1.25V(65)	20	CL536-0571-0-65	18.35	11.25	14.95
DF13EA-30DP-1.25V(65)	30	CL536-0572-0-65	24.60	17.50	21.20
DF13EA-40DP-1.25V(65)	40	CL536-0573-0-65	30.85	23.75	27.45



NOTES 1: If there are pattern and a bia hole on  part, there is a possibility that it will make contact with the leads.
2: Lead co-planality include reinforced metal fittings shall be 0.1mm MAX.

2	Brass	Contact area:Gold plated 0.2μm MIN	5	ELASTOMER	Gray
		Lead area:Tin plated 1μm MIN	4	R. PVC	Electrostatic protection: Clear
		Under plating:Nickel 1μm MIN	3	Phosphor bronze	Tin plated 1μm MIN
1	Polyamide	Beige, UL94V-0	NO.	MATERIAL	FINISH . REMARKS
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE

 HIROSE ELECTRIC CO., LTD.	APPROVED :HS. OKAWA	20200330	DRAWING NO.	EDC-367982-65-00	
	CHECKED :TS. KUMAZAWA	20200330	PART NO.	DF13EA- *DP-1. 25V<65>	
	DESIGNED :HK. HAYASHI	20200330	CODE NO.	CL536-	
	DRAWN :DS. HIROWATARI	20200326		 1/2	

