

AV98A176
CONNECTION TECHNOLOGY • CABLE SOCKETS / CONNECTORS PRE-ASSEMBLED ON TWO SIDES

accessories, , Suitable for self-assembly, 1.5m, Valve connector type A Female (socket) 3pin Angular, M12 Male (plug) 3pin Straight, 3x0.5mm², PUR (Polyurethane), With LED display


MECHANICAL FEATURES

Cable infeed of A connection	Angular
Cable infeed of B connection	Straight
Cable length	1.5 m
Material of cable sheath	PUR (Polyurethane)
Number of cores	3
Version	Connection cable
Wire cross section	0.5 mm ²

ELECTRICAL FEATURES

Number of pins of A connection	3
Number of pins of B connection	3
Suitable for self-assembly	+
Type of A electrical connection	Valve connector type A
Type of B electrical connection	M12
Type of plug-in contact, A connection	Female (socket)
Type of plug-in contact, B connection	Male (plug)
With LED display	+

OTHER FEATURES

IR-networked	-
--------------	---

Other


Packaging dimensions	160mm x 30mm x 240mm
Shipping weight	0.09kg
Tariff code	85444290

Classification


ipf product group	700
eClass 8.0	27279218
eClass 9.0	27060311
eClass 9.1	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855

Connection

male connection



female connection



Dimensional drawing

Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.