


IN18A584**INDUCTIVE SENSORS • ATMOSPHERIC-CHANGE RESISTANT**

sensor inductive, M18x1 75long, Non-flush, Sn: 7, 10-33V DC, -55°C,
PNP NO, Cable 2m FEP, IP69K, V4A

**MECHANICAL FEATURES**

Active area material of sensor	Polytetrafluorethylene (PTFE)
Alignment of cable entry	Axial
Ambient temperature	-55 °C ... 60 °C
Ambient temperatures < -25°C	+
Cable infeed	Axial
Cable length	2 m
Degree of protection (IP)	IP69K
Design	Cylinder, screw-thread
Housing material	Stainless steel 1.4571
Material of cable sheath	FEP
Mechanical mounting condition for sensor	Non-flush
Pressure-proof	-
Sensor length	75 mm
Thread length	35 mm
Thread pitch	1 mm
Thread size, metric	18
Wire cross section	0.75 mm ²

ELECTRICAL FEATURES

Cascadable	-
No-load current	4 mA
Norm measuring plate	18x18x1
Rated switching current	200 mA
Reverse polarity protection	+
Short-circuit protection	+
Suitable for safety functions	-
Supply voltage	10 V ... 33 V
Switching distance	7 mm
Switching frequency	1000 Hz
Type of electrical connection	Cable
Type of switching function	Normally open contact
Type of switching output	PNP
Voltage drop	2 V

ELECTRICAL FEATURES

Voltage type	DC
With LED display	+
With monitoring function of downstream devices	-


Other

Packaging dimensions	124.0mm x 28.0mm x 149.0mm
Shipping weight	0.15kg
Tariff code	85365019

Classification

ipf product group	700
eClass 8.0	27270101
eClass 9.0	27270101
eClass 9.1	27270101
ETIM-5.0	EC002714
ETIM-6.0	EC002714
ETIM-7.0	EC002714

Connection



Dimensional drawing

Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.