


VK000052
CONNECTION TECHNOLOGY • DISTRIBUTION TERMINALS

distributor, 33x15x40mm, Parallel wiring, 2x M8 3pin, 60V, M8 3pin, IP67


MECHANICAL FEATURES

Degree of protection (IP)	IP67
Fix cable version suitable for trailing chain	-
Height	33 mm
Housing color	Black
Length	15 mm
Width	40 mm

ELECTRICAL FEATURES

Cable length, configurable	-
Connection for NPN sensors	-
Max. ampacity per I/O signal	4 A
Max. total current	4 A
Number of pins	3
Number of pins of sensor/actuator slots	3
Number of sensor/actuator slots	2
Rated switching current	4000 mA
Rated voltage	60 V
Type of branches for sensor/actuator cables	M8
Type of plug connector for trunk line	M8
Voltage type	AC/DC
With LED display	-
With potential separation	-

OTHER FEATURES

Operating temperature	-25 °C ... 85 °C
-----------------------	------------------


Other

Packaging dimensions	100mm x 18.0mm x 120mm
Shipping weight	0.02kg
Tariff code	85366990


Classification

ipf product group	855
eClass 8.0	27279219
eClass 9.0	27440108
eClass 9.1	27440108
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585

Connection



Dimensional drawing



Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.