


HSS-HF 3/8 5.8-8.0/50Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 5.8 - 8 mm, 50.8 x 16 mm, yellow
Order No.	1961930000
Type	HSS-HF 3/8 5.8-8.0/50Y
GTIN (EAN)	4032248642625
Qty.	2,000 pc(s).
compatible printer	2599430000 2599440000 1140490000

Creation date January 25, 2021 11:56:21 AM CET

Catalogue status 15.01.2021 / We reserve the right to make technical changes.

HSS-HF 3/8 5.8-8.0/50Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	0.77 mm	Depth (inches)	0.03 inch
Height	50.8 mm	Height (inches)	2 inch
Net weight	1.34 g	Width	16 mm
Width (inches)	0.63 inch		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

General data

Colour	yellow	Halogen	No
Material	Polyolefine	Material colour according to resistance code	4
Operating temperature range	-55...105 °C	Operating temperature range, max.	105 °C
Operating temperature range, min.	-55 °C	Recommended industries	Transportation
Type of printing	neutral	Width	16 mm

Conductor and cable markers

Conductor O.D.	5.8 - 8 mm	Conductor O.D., max.	8 mm
Conductor O.D., min.	5.8 mm	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	10 mm ²	Cross-section for connected wire	10 - 16 mm ²
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Text field height	15.25 mm
Text field width	50.8 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN 45545-2 2013+A1 2015 BS EN ISO 4589-2 1999
Engineering Data	STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S

HSS-HF 3/8 5.8-8.0/50Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

