

HELUcond PE Corrugated tubes, polyethylene

Weak stress



HELUcond PE-F / PE-B

Cable protection tube for weak stress applications.

Capacity/100mm NW 17: approx. 200 N

Application

- Plant and machine construction
- Automation technology
- Installation technology
- Control cabinet construction

Material

Mod. Polyethylene

Flammability acc. to UL 94: HB

- halogen-free

Properties

- Resistant to bases.

Note

Suitable connection glands:
HELUquick.

Technical data

Temperature range: -40°C up to +70°C

Temperature range temporary up to +90°C

Fine profile / PE-F

Part no. grey	Part no. black	Nominal size mm	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/100 metres at a purchase of		
						up to 100	101 - 500	501 - 1000
91621	90448	10,0	9,8	12,7	50	o. r.	o. r.	o. r.
90433	90449	12,0	11,6	15,6	50	o. r.	o. r.	o. r.
90435	90451	17,0	16,3	20,8	50	o. r.	o. r.	o. r.
90436	90452	23,0	22,9	27,9	50	o. r.	o. r.	o. r.
90437	90453	29,0	28,9	34,0	25	o. r.	o. r.	o. r.
90438	90454	37,0	33,5	41,5	25	o. r.	o. r.	o. r.
90439	90455	50,0	45,2	53,4	25	o. r.	o. r.	o. r.

Coarse profile / PE-B

Part no. grey	Part no. black	Nominal size mm	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/100 metres at a purchase of		
						up to 100	101 - 500	501 - 1000
93781	93786	21,0	21,7	28,0	50	o. r.	o. r.	o. r.
93782	93787	29,0	28,5	34,5	25	o. r.	o. r.	o. r.
93783	93788	36,0	36,0	42,4	25	o. r.	o. r.	o. r.
93784	93789	48,0	47,7	54,5	25	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request