

Technical drawing of a 90-degree elbow fitting. The drawing shows the side profile of the fitting, which has a hexagonal nut and a flange. Dimensions are indicated by arrows and labeled with letters:

- N**: Total length of the fitting.
- M**: Length of the flange section.
- L**: Length of the elbow section.
- O**: Diameter of the elbow section.
- K**: Diameter of the flange section.
- P**: Total diameter of the fitting.

Artikelbezeichnung/ Product type	Nom. Schlauch-Ø/ Nom. Conduit-Ø	Gewinde/Thread K	L	M	SW / A/F N	Lichte Weite/Bore O	SW / A/F P	Projektnr./ Project no.
PCS12-90FMC-M16	12	M16x1.5	10	18	22	8.6	20	GPN 11-0287
PCS16-90FMC-M16	16	M16x1.5	10	18	26	11.5	20	GPN 11-0288
PCS16-90FMC-M20	16	M20x1.5	13	20	26	11.5	24	GPN 11-0289
PCS20-90FMC-M20	20	M20x1.5	13	20	29	15.3	24	GPN 11-0290
PCS25-90FMC-M25	25	M25x1.5	14	25	35	19.1	30	GPN 11-0291
PCS32-90FMC-M32	32	M32x1.5	15	31	42	26.0	36	GPN 11-0292

mit integrierter Dichtung (bildlich nicht dargestellt)/
with integrated seal (not visually represented)

Ausdruck nur zur Information /
Printed copy for information only

Sheet
Page 1 / 1
Blatt