







PC MOUNTING



CIRCUIT: SPST ▲

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: SILVER W/ STAINLESS STEEL DOME
5. RATING: 12VDC, 50mA
- ▲ 6. OPERATING FORCE: 160 ± 50 gf
7. TRAVEL: 0.25 ± 0.2 / -0.1mm
8. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
9. MECHANICAL/ELECTRICAL LIFE 1,000,000 CYCLES MIN.
10. ▲ DENOTES CRITICAL PARAMETER
11. PACKAGING: 1,000 PIECES PER POLY BAG
12. OPERATING TEMP: -40°C TO 85°C



D	24548	REMOVE STEP IN HOUSING, CHANGE TEMP	10/19/20	JM
C	23683	drawing update, 7.40 to 7.10	11/27/18	MW
B	18853	REVISE LIFE EXPECTANCY (WAS 100,000)	2/5/10	BLR
A	18700	RELEASED FOR PRODUCTION	11/6/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®

TITLE	TL1105VF160QSSDOME
-------	--------------------

SCALE
4:1

DATE	11/6/2009
------	-----------

DR	BLR
----	-----

DWG	P010250
-----	---------

REV
D