

Product information

64 62 120

Electronics End Cutting Nipper

DIN ISO 9654



MM  $\angle 65^\circ$

- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction-hardened, cutting edge hardness at least 56 HRC
- Oblique End Cutter, mini-blade with small bevel, $\alpha = 65^\circ$
- High-grade special tool steel, forged, oil-hardened

General

Article No.	64 62 120
EAN	4003773046998
Head	mirror polished
Handles	with multi-component grips
weight	77 g
Dimensions	120 x 71 x 17 mm
Standard	DIN ISO 9654


Technische Attribute

Cutting capacities soft wire (diameter)	Ø 0.6 mm
Head width	11 mm
	20 mm
	7 mm
	7 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002222
ETIM 6.0	EC002222
proficl@ss 6.0	AAA947c004
UNSPSC 13.1	27112117

technical change and errors excepted



64 62 120