


sg09615



Description

- Photovoltaic - Switch-disconnectors
- Acc .to EN 60947-3 DC-PV1 or DC-PV2 resp.
- Very compact
- Improved reliability due to independent manual operation
- Stable performance at any load current
- Polarity independent
- Only one path per pole => lower power loss



sg09615

Rated operating current I_e
(A)Type
Designation

Article No.

Units per
package**2-poles with rotary handle, 600 V**

16	PV-DIS-06-16/2-ROT	179259	1
32	PV-DIS-06-32/2-ROT	179260	1
63	PV-DIS-06-63/2-ROT	179261	1
100	PV-DIS-06-100/2-ROT	185503	1
125	PV-DIS-06-125/2-ROT	179262	1

2-poles with rotary handle, 800 V

16	PV-DIS-08-16/2-ROT	179263	1
32	PV-DIS-08-32/2-ROT	179264	1
63	PV-DIS-08-63/2-ROT	179265	1
100	PV-DIS-08-100/2-ROT	185504	1
125	PV-DIS-08-125/2-ROT	179266	1

2-poles with rotary handle, 1000 V

16	PV-DIS-10-16/2-ROT	179267	1
32	PV-DIS-10-32/2-ROT	179268	1
63	PV-DIS-10-63/2-ROT	179269	1
100	PV-DIS-10-100/2-ROT	185505	1
125	PV-DIS-10-125/2-ROT	179270	1

2-poles without rotary handle, 600 V

16	PV-DIS-06-16/2	179255	1
32	PV-DIS-06-32/2	179256	1
63	PV-DIS-06-63/2	179257	1
100	PV-DIS-06-100/2	185502	1
125	PV-DIS-06-125/2	179258	1

Technical Data

	PV-DIS-06...	PV-DIS-08...	PV-DIS-10...
Rated operating voltage	600 V	800 V	1000 V
Rated impulse withstand voltage	4 kV	6 kV	6 kV
	PV-DIS-.../2	PV-DIS-.../2-ROT	
Rated insulation voltage	630 V	1000 V	
Utilization category (acc. to EN 60947-3)			
Rated operating current I _b 16-100 A	DC-PV2		
Rated operating current I _b 125 A	DC-PV1		
Mechanical operations	acc. to IEC 60947-3 Category of utilization DC-PV2 or DC-PV1		
Electrical operations	acc. to IEC 60947-3 Category of utilization DC-PV2 or DC-PV1		
Rated frequency / Operating frequency	DC only		
Approbation	ÖVE, VDE		
Resistance to climatic conditions according to	IEC 60947-2		
Shock resistance, Vibration resistance acc. to	IEC 60947-2		
Dimensions	according to drawing		
Dimensions of terminals	2.5-50 mm ²		
Cable material	Cu		
Degree of protection	IP20		
Degree of protection, built-in	IP40		
Mounting position	all the same		
Ambient temperature range	-20 to +40 °C, 40 to 75 °C Derating		
Storage Temperature	-40 to +75 °C		
Max. DC contact rating	100 %		
Safe electrical isolation	yes		

Dimensions (mm)

