

21700144	DATA SHEET	
Valid from: 27.10.2020	ETHERLINE® ACCESS UF(P*)T	

Description

- Fast Ethernet Network-Switch (10/100BaseT(X)), unmanaged
- Ports: RJ45
- Space-saving design for DIN rail
- Designed for industrial environment (protection class IP20)
- PROFINET Conformance Class A (only 8/16 port)



General characteristics

Interfaces	RJ45 Port: 10/100BaseT(X) auto-negotiation, full-/halfduplex-mode and Auto-MDI/MDI-X-connection
Switch properties	MAC-table size: 1 K (UF05-T) 16 K (UF08-T) 2x 16 K (UF16-T) Packet puffer size: 512 Kbit (UF05-T) 2048 Kbit (UF08-T) 2x 2048 Kbit (UF16-T) Protocol: LLDP & PTCP Delay-Traffic Blocking (UF08-T & UF16-T) operating temp.: -25°C to +75°C (-13°F to 167°F) storage temp.: -40°C to +85°C (-40°F to 185°F)
Temperature range	
Relative humidity	5% to 95 % (non-condensing)
Pollution degree	2
Standards	IEEE 802.3i (10BaseT) IEEE 802.3u (100BaseTX) IEEE 802.3x (Flow control) IEEE 802.1Q (QoS) (UF08-T & UF16-T)
Processing type	Store and Forward
MTBF (mean time between failures)	311.418 Std @ MIL-HDBK-217 (UF05T) 260.172 Std @ MIL-HDBK-217 (UF08T) 145.591 Std @ MIL-HDBK-217 (UF16T)

Variation

Article	Description	Ports (P*) [amount]
21700144	ETHERLINE ACCESS UF05T	05
21700145	ETHERLINE ACCESS UF08T	08
21700146	ETHERLINE ACCESS UF16T	16

Creator: FELI1/PDP Released: IVSE1/PDP	Document: DB21700144EN Version: 03	Page 1 of 3
---	---------------------------------------	-------------

21700144	DATA SHEET	
Valid from: 27.10.2020	ETHERLINE® ACCESS UF(P*)T	

Power requirements


Input voltage	24 V DC (18-30V DC)
Input current (max.) at +24 V DC	60 mA (UF05T) 100 mA (UF08T) 100 mA (UF16T)
Reverse polarity protection	support
Overload voltage protection	support

Physical properties


IP class	IP20
Weight	0.11 kg (UF05T) 0.15 kg (UF08T) 0.27kg (UF16T)
Installation	DIN-rail mounting

Technical drawing

Dimensional drawing (UF05T)




Dimensional drawing (UF08T)



Creator: FELI1/PDP Released: IVSE1/PDP	Document: DB21700144EN Version: 03	Page 2 of 3
---	---------------------------------------	-------------

21700144	DATA SHEET	
Valid from: 27.10.2020	ETHERLINE® ACCESS UF(P*)T	

Dimensional drawing (UF16T)



Standards and approvals

EMC

DIN EN 61000-6-2

Approvals

DIN EN 61000-6-4

CE

PROFINET

UL (E331560)

Conformance Class A (UF08T /UF16T)

Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: FELI1/PDP Released: IVSE1/PDP	Document: DB21700144EN Version: 03	Page 3 of 3
---	---------------------------------------	-------------