





ISS.	AMEND	DATE
1	1st DRAWN	07/09/90
2	UPDATED	02/02/16
3	UPDATE / REDRAWN	06/10/21

SPECIFICATIONS


Contact Resistance : 30mΩ max
Insulation Resistance : 100MΩ min. at DC 500V
Dielectric Withstanding Voltage: AC 500V for one minute

TOLERANCE :±0.3mm UNLESS OTHERWISE SPECIFIED



NUT SUPPLIED UNASSEMBLED

6.	M4x0.5 Nut	Brass	1	Nickel Plated
5.	Housing	PBT 4815 UL-94 V0	1	Black
4.	M4x0.5 Nose	Brass	1	Nickel Plated
3.	Break Contact	0.3T Brass	1	Silver Plated
2.	Spring Contact	0.25T Phosphor Bronze	1	Silver Plated
1.	Earth Terminal	0.3T Brass	1	Silver Plated
No.	Description	Material	Qty	Finish



RoHS
COMPLIANT

TOLERANCE
NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±
HOLE Ø ±
ANGLES ±
UNLESS
OTHERWISE STATED