


Hexalobular (6 Lobe) socket flat countersunk head partial thread and cutting ribs under the head

BN 20699



Headform	Countersunk
Drive	Hexalobular socket
Thread	partially threaded
Material	Steel
Material execution	case-hardened
Surface	zinc plated blue, added lubricant
Warnings	ISO 4042 Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement! Further notice to residual risks can be found in the introduction section.

Article no	d1	L	d2 max	k~	Hexalobular socket	b
3675830	4.5	45	9	3.8	X20	27
3675832	4.5	60	9	3.8	X20	36
3675834	4.5	80	9	3.8	X20	48
3675836	5	35	10	4.2	X25	21
3675838	5	45	10	4.2	X25	27
3675807	3	25	6	2.6	X10	16
3675808	3	30	6	2.6	X10	18
3675809	3	35	6	2.6	X10	21
3675811	3	40	6	2.6	X10	24
3675812	3	45	6	2.6	X10	27
3675813	3.5	30	7	2.8	X15	18
3675814	3.5	35	7	2.8	X15	21
3675815	3.5	40	7	2.8	X15	24
3675816	3.5	45	7	2.8	X15	27

Article no	d1	L	d2 max	k~	Hexalobular socket	b
3675817	3.5	50	7	2.8	X15	30
3675818	4	30	8	3.6	X20	18
3675819	4	35	8	3.6	X20	21
3675820	4	40	8	3.6	X20	24
3675821	4	45	8	3.6	X20	27
3675822	4	50	8	3.6	X20	30
3675823	4	60	8	3.6	X20	36
3675824	4	70	8	3.6	X20	42
3675825	4	80	8	3.6	X20	48
3675826	4.5	30	9	3.8	X20	18
3675827	4.5	35	9	3.8	X20	21
3675829	4.5	40	9	3.8	X20	24
3675831	4.5	50	9	3.8	X20	30
3675833	4.5	70	9	3.8	X20	42
3675835	5	30	10	4.2	X25	18
3675837	5	40	10	4.2	X25	24
3675839	5	50	10	4.2	X25	30
3675840	5	60	10	4.2	X25	36
3675841	5	70	10	4.2	X25	42
3675842	5	80	10	4.2	X25	48
3675843	5	90	10	4.2	X25	54
3675844	5	100	10	4.2	X25	60
3675845	5	110	10	4.2	X25	72
3675847	5	120	10	4.2	X25	72
3675848	6	50	12	4.6	X30	30
3675849	6	60	12	4.6	X30	36
3675850	6	70	12	4.6	X30	42
3675851	6	80	12	4.6	X30	48
3675852	6	90	12	4.6	X30	54
3675853	6	100	12	4.6	X30	60
3675854	6	110	12	4.6	X30	72
3675855	6	120	12	4.6	X30	72
3675856	6	130	12	4.6	X30	72
3675857	6	140	12	4.6	X30	72
3675858	6	150	12	4.6	X30	72
3675859	6	160	12	4.6	X30	72