



Cable Ties inside serrated with tuckaway


The RT250 is a releasable cable tie. Due to its minimum loop tensile strength of 1,115 N the cable tie is perfectly suited to fix larger and/or heavier bundles. RT250 can be opened and re-used. UV resistant cable ties manufactured from PA66W are recommended for outdoor applications. For shorter lengths REL250-Series can be offered.

Features and benefits

- Releasable and reusable cable tie
- Suitable for larger and/or heavier bundles
- Eyelet allows excess tail to be tucked neatly away
- Available in black and natural colour
- Extended trigger for simple and quick release of ties
- Protected trigger to avoid accidental release
- RT250 cable ties are inside serrated



Ideal for larger or heavier bundles these ties can be opened and reused.




RT250-Series

RT250-Series

TYPE	Width (W)	Length (L)	Bundle Ø max.	N	Material	Colour	Pack Cont.	Article-No.
RT250M	12.5	565.3	150.0	1,115	PA66	Black (BK)	25 pcs.	131-75610
	12.5	565.3	150.0	1,115	PA66	Natural (NA)	25 pcs.	131-75619
	12.5	565.3	150.0	1,115	PA66W	Black (BK)	25 pcs.	131-75620
RT250XL	12.5	1,030.0	305.0	1,115	PA66	Black (BK)	25 pcs.	131-75510
	12.5	1,030.0	305.0	1,115	PA66	Natural (NA)	25 pcs.	131-75519

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



Releasable cable tie REL250-Series

REL250-Series

TYPE	Width (W)	Length (L)	Bundle Ø max.	N	Material	Colour	Pack Cont.	Article-No.
REL250S	12.2	230.0	50.0	1,115	PA66HIR(S)	Black (BK)	50 pcs.	111-00074
REL250X	12.2	385.0	100.0	1,115	PA66HIR(S)	Black (BK)	50 pcs.	111-00075

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Material Specification Overview

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Aluminium-alloy	AL	-40 °C to +180 °C	Natural (NA)		- Corrosion resistant - Antimagnetic	RoHS
Chloroprene	CR	-20 °C to +80 °C	Black (BK)		- Weather-resistant - High yield strength	RoHS
Ethylene Tetrafluoroethylene (Tefzel®)	E/TFE	-80 °C to +170 °C	Blue (BU)	UL 94 V0	- Resistance to radioactivity - UV-resistant, not moisture sensitive - Good chemical resistance to: acids, bases, oxidizing agents	RoHS
Polyacetal	POM	-40 °C to +90 °C, (+110 °C, 500 h)	Natural (NA)	UL 94 HB	- Limited brittleness sensitivity - Flexible at low temperature - Not moisture sensitive - Robust on impacts	RoHS
Polyamide 11	PA11	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Bio-plastic, derived from vegetable oil - Strong impact resistance at low temperature - Very low moisture absorption - Weather-resistant - Good chemical resistance	HF RoHS
Polyamide 12	PA12	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Good chemical resistance to: acids, bases, oxidizing agents - UV-resistant	HF RoHS
Polyamide 4.6	PA46	-40 °C to +150 °C (5000 h), +195 °C (500 h)	Natural (NA), Grey (GY)	UL 94 V2	- Resistance to high temperatures - Very moisture sensitive - Low smoke sensitiv	HF LFH RoHS
Polyamide 6	PA6	-40 °C to +80 °C	Black (BK)	UL 94 V2	High yield strength	RoHS
Polyamide 6, high impact modified	PA6HIR	-40 °C to +80 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6	PA66	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK), Natural (NA)	UL 94 V2	High yield strength	HF RoHS
Polyamide 6.6, glass-fibre reinforced	PA66GF13, PA66GF15	-40 °C to +105 °C	Black (BK)	UL 94 HB	Good resistance to: lubricants, vehicle fuel, salt water and a lot of solvent	HF RoHS
Polyamide 6.6, heat and UV stabilised	PA66HSW	-40 °C to +105 °C	Black (BK)	UL 94 V2	- High yield strength - Modified elevated max. temperature - UV-resistant	HF RoHS
Polyamide 6.6, heat stabilised	PA66HS	-40 °C to +105 °C	Black (BK), Natural (NA)	UL 94 V2	- High yield strength - Modified elevated max. temperature	HF RoHS
Polyamide 6.6, high impact modified	PA66HIR	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6, high impact modified, heat and UV stabilised	PA66HIRHSW	-40 °C to +110 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature - Modified elevated max. temperature - High yield strength, UV-resistant	RoHS
Polyamide 6.6, high impact modified, heat stabilised	PA66HIRHS	-40 °C to +105 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature - Modified elevated max. temperature	RoHS
Polyamide 6.6, high impact modified, ScanBlack	PA66HIR(S)	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6, UV-resistant	PA66W	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 V2	- High yield strength - UV-resistant	HF RoHS

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Polyamide 6.6, with metal particles	PA66MP	-40 °C to +85 °C, (+105 °C, 500 h)	Blue (BU)	UL 94 HB	• High yield strength • Metal and X-Ray detectable	HF RoHS
Polyamide 6.6, with metal particles	PA66MP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	• High yield strength • Metal and x-ray detectable	HF RoHS
Polyamide 6.6 V0	PA66V0	-40 °C to +85 °C	White (WH)	UL 94 V0	• High yield strength • Low smoke emission	HF LFH RoHS
Polyester	SP	-50 °C to +150 °C	Black (BK)	halogen free	• UV-resistant • Good chemical resistance to: most acids, alkalis and oils	HF LFH RoHS
Polyetheretherketone	PEEK	-55 °C to +240 °C	Beige (BGE)	UL 94 V0	• Resistance to radioactivity • Not moisture sensitive • Good chemical resistance to: acids, bases, oxidizing agents	HF LFH RoHS
Polyethylene	PE	-40 °C to +50 °C	Black (BK), Grey (GY)	UL 94 HB	• Low moisture absorption • Good chemical resistance to: most acids, alcohol and oils	HF RoHS
Polyolefin	PO	-40 °C to +90 °C	Black (BK)	UL 94 V0	• Low smoke emissions	HF LFH RoHS
Polypropylene	PP	-40 °C to +115 °C	Black (BK), Natural (NA)	UL 94 HB	• Floats in water • Moderate yield strength • Good chemical resistance to: organic acids	HF RoHS
Polypropylene, Ethylene-Propylene- Dien-Terpolymere- rubber free of Nitrosamine	PP, EPDM	-20 °C to +95 °C	Black (BK)	UL 94 HB	• Good resistance to high temperatures • Good chemical and abrasion resistance	HF RoHS
Polypropylene with metal particles	PPMP	-40 °C to +115 °C	Blue (BU)	UL 94 HB	• Metal and X-Ray detectable • Heat resistant • Moderate yield strength • Good chemical resistance	RoHS
Polypropylene with metal particles	PPMP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	• High yield strength • Metal and x-ray detectable	HF RoHS
Polyvinylchloride	PVC	-10 °C to +70 °C	Black (BK), Natural (NA)	UL 94 V0	• Low moisture absorption • Good chemical resistance to: acids, ethanol and oil	RoHS
Stainless Steel	SS304, SS316	-80 °C to +538 °C	Natural (NA)	non-burning	• Corrosion resistant • Antimagnetic • Weather resistant • Outstanding chemical resistance	HF LFH RoHS
Thermoplastic Polyurethane	TPU	-40 °C to +85 °C	Black (BK)	UL 94 HB	• High elastic • Good chemical resistance to: acids, bases and oxidizing agents	HF RoHS

Tefzel® is a registered trademark of DuPont. General linguistic usage for cable ties made from raw material E/TFE is Tefzel®-Tie. In addition to Tefzel® from DuPont HellermannTyton is also using equivalent E/TFE raw material from other suppliers. *These details are only rough guide values. They should not be regarded as a material specification and are no substitute for a suitability test. Please see our datasheets for further details.

**More colours on request.



N = Minimum Loop Tensile Strength
for Cable Ties (Newton)

HF = Halogenfree

LFH = Limited Fire Hazard

RoHS = Restriction of Hazardous Substances