

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731070060

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell without Dimples, 7 Circuits, 5 Signal Contacts Loaded

Documents:

Drawing (PDF)

Datasheet (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

IP Rating

Overview

Product Category

Product Name

Taxonomy

Type

UPC

D-Sub Products

173107

IP20

FCT D-Sub Connectors

D-Sub Connector

FCT Products

D-Sub Connectors

Mixed Layout

889056316996

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Gender

Material - Contact

Material - Resin

Material - Shell

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Panel Mount

Panel Mount Method

Pitch - Mating Interface

Pitch - Termination Interface

Plating - Contact

Plating - Shell

Plating min - Mating

Polarized to Mating Part

Ports

Shielded

Temperature Range - Operating

Termination Style

Waterproof / Dustproof

Waterproof / Dustproof Type

Wire Size AWG

5

7

Green

500

Female

Copper Alloy

PBT

Steel

6.700/g

2

Straight

No

None

Carton

Rear

Flange

2.84mm

2.84mm

Gold over Nickel

Tin

0.800µm

Yes

1

Yes

-55° to +130°C

Solder Cup

No

IP20

20

Electrical

Current - Maximum per Contact

7.5A

Material Info

Engineering Number

FM7W2S-K121



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

173107 Series

Mates With

FCT Mixed Layout D-Sub, Size 2, 7W2, Plug

Use With

FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

Reference - Drawing Numbers
Sales Drawing

1731070060-000

This document was generated on 01/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION