

VENIFISH VE990



LATEX ON INTERLOCK COTTON LINING GLOVE - LENGTH: 30 CM

Ref. VE990OR



Product specifications

Latex on interlock cotton lining. Rough-textured hand. Length: 30 cm. Thickness: 1,80 mm.

Support: 100% Interlock cotton.

Coating: 100% natural latex.

COLOUR

Orange

SIZE

7/8, 8/9, 9/10, 10/11

Product Use - Risks



Heat



BIOLOGICAL



Wearing



CHEMICAL



PARTICULES



Construction / Civil engineering



Heavy industry

CHEM D-FINDER



Product's highlights & user's benefits



100°C

Versatile glove

Resistance to chemicals and contact heat of 100°C for 15 seconds



Structure on very rough palm

Excellent grip of very slippery objects

Cut cotton interlock stitched

Absorption of perspiration and moisture for improved comfort in everyday life

Certifications and Standards



REGULATION (EU) 2016/425

EN420:2003+A1:2009 General requirements

5: Dexterity (from 1 to 5)

EN388:2016 Protective gloves against mechanical Risks (Levels obtained on the palm)

3: Resistance to abrasion (from 1 to 4)

1: Resistance to cutting (from 1 to 5)

2: Resistance to tear (from 1 to 4)

1: Resistance to puncture (1 to 4)

X: Resistance to cutting by sharp objects (TDM EN ISO 13997) (from A to F)



EN407:2004 Protective gloves against Heat & Fire risks (X = Unrealized test)

X: Resistance to flammability (from 1 to 4)

1: Contact heat resistance (from 1 to 4)

X: Convective heat resistance (1 to 4)

X: Radiant heat resistance (from 1 to 4)

X: Small splashes of molten metal (from 1 to 4)

X: Large quantities of molten metal (from 1 to 4)



EN ISO 374-1:2016 Protective gloves against dangerous chemicals and micro-organisms - Part 1: Terminology and performance requirements for chemical risks.

TYPE A: Type A - Water and air tightness according to EN ISO 374-2:2019. Permeation resistance to at least 6 chemicals at level 2 according to EN16523-1: 2015, .. Determination of resistance to degradation by chemicals according to EN ISO 374-4: 2019. Part 4: Determination of resistance to degradation by chemicals.

A 6 > 480 mn: Méthanol (A) CAS 67-56-1

K 6 > 480 mn: Caustic soda 40% (K) CAS 1310-73-2

L 4 > 120 mn: Sulphuric acid 96 % (L) CAS 7664-93-9

M 5 > 240 mn: Nitric acid 65% (M) CAS 7697-37-2

N 4 > 120 mn: Acetic acid 99% (N) CAS 64-19-7

P 6 > 480 mn: Hydrogen peroxide 30% (P) 7722-84-1

T 6 > 480 mn: Formaldehyde 37% (T) CAS 50-00-0



EN ISO 374-5:2016 Protective gloves against dangerous chemicals and micro-organisms - Part 5: Terminology and performance requirements against micro-organisms risks.

BACTERIA + FUNGI .. BACTERIA + FUNGI : Water and air tightness according to EN ISO 374-2:2019.



REGULATION (EU) 1935/2004 CONTACT WITH FOOD PRODUCTS

GLOB MIGR Food contact - Overall Migration

.. Contact with any type of food

References

References	Bar code	COLOUR	SIZE		
VE990OR07	3295249024116	Orange	7/8	120	12
VE990OR08	3295249024123	Orange	8/9	120	12
VE990OR09	3295249024130	Orange	9/10	120	12
VE990OR10	3295249024147	Orange	10/11	120	12