

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0019091039

Status:

Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing with Positive Latch, 94V-2, 3 Circuits

Documents:

3D Model

3D Model (PDF)


Drawing (PDF)

Product Specification PS-3191-001-001 (PDF)

Packaging Specification 31910001-PK-000 (PDF)

Packaging Specification PK-3191-001-001 (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	3191
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 50361689; Polarized to Mating Part, without Mounting Ears
Overview	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
Taxonomy	Connector Housings
UPC	800753594487
Physical	
Breakaway	No
Circuits (maximum)	3
Circuits Detail	1x3
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.885/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	11.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	3191-3R1
Reference - Drawing Numbers	
Packaging Specification	31910001-PK-000, PK-3191-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

3191 Series

Mates With

19092036 , 19092037 , 19092038 , 19092039 , 5219

Use With

Standard .093" Female Crimp Terminals 1189 , 1381 , 1433 , 4550 . Standard .093" Male Crimp Terminals 1190 , 1380 , 1434 , 1973 , 42138

This document was generated on 10/07/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION