

DCM340 Digital clamp meter



- DC and AC current and voltage
- 600 A and 600 V
- Resistance and continuity
- 3½ digit, 4000 count display with backlight
- High resolution digital bargraph
- Peak, min/max and data-hold functions

DESCRIPTION

The DCM340 is a highly versatile instrument and ideal for use in the installation, maintenance, monitoring or checking of a.c. or d.c. electrical systems and equipment.

There are four instruments in the DCM series of clamp-meters, including the 400 A a.c. current-only DCM310; the DCM320 which includes voltage and resistance measurement; the DCM330 Fork-Multimeter, which is an open fixed jaw design; and this, the DCM340. Capable of measuring a.c. and d.c. current up to 600 A; a.c. and d.c. voltage up to 600 V; resistance up to 400 Ω ; and frequency up to 400 Hz, the DCM340 is the most versatile in the range.

Current measurement combined with the comprehensive and accurate multimeter functions of the DCM340 eliminate the need to carry around both a clampmeter and multimeter - this instrument does it all.

The large clear digits of the numeric display are complemented by the high-resolution digital bar graph, useful for indicating trending and fluctuation of measurement. The backlight assists use in poorly lit areas such as distribution cupboards and corners of switchrooms; and the data-hold feature enables use on difficult access cables where otherwise the display may be impossible to see.

Min/Max hold provides the ability to store the maximum and minimum d.c. or rms values over a period of time. While storage is taking place, either the present, maximum or minimum value can be displayed. Peak hold stores the maximum and minimum peak value of an a.c. signal at a 10 ms sample rate.

The auto-off feature automatically places the meter in power-save mode after 30 minutes from power-on, but this can be disabled if required for min/max measurements.

Using the Relative mode (REL), a stable value can be stored, the instrument zeroed at that point, and then any variation from that value is displayed as a direct measurement relative to it.

The DCM340 is safety rated to IEC 61010-1 Cat III 600 V, and is drop-tested to 1.2 m onto a hard floor. It is supplied with test leads and a carry case, and a full 1-year manufacturer's warranty.

APPLICATION

The DCM340 is designed to be used on electrical systems and equipment where there is a need to measure current, volts, resistance and frequency. It is therefore intended for use while installing, maintaining, fault-finding or monitoring those systems.

The min/max and peak-hold enable maximum load currents from equipment to be identified such as start-up currents to motors and heaters.

With the added benefit of d.c. current measurement, it can also be used in applications including domestic power generation from solar panels and wind-turbines; battery monitoring; automotive uses for charging and load circuits; electric vehicle servicing such as fork-lift trucks; lift maintenance; UPS commissioning, servicing and maintenance; electro-plating plants and welding equipment servicing.

SPECIFICATION

Base specifications only. For detailed specification, refer to User Guide
All accuracies specified at 23°C ±5° <80%Rh

AC current

Range	Accuracy 50 - 60Hz	Accuracy 61 - 400Hz
0-60.0 A	±1.9% ±7 digits	±2.5% ±7 digits
60.0 - 400.0 A	±1.9% ±5 digits	±2.5% ±5 digits
400 - 600 A	±2.5% ±5 digits	±2.9% ±5 digits

DC current

Range	Accuracy
0 - 60.0 A	±1.5% ±10 digits
60.0 - 400.0 A	±1.9% ±5 digits
400 - 600 A	±1.9% ±10 digits

Voltage

50 - 500Hz DC

Range	Accuracy	Accuracy
0 - 400.0 V	±1.0% ±5 digits	±0.7% ±2 digits
400 - 600 V	±1.0% ±5 digits	±0.7% ±2 digits

Input impedance 1 MΩ // < 100 pF

Winding resistance

Range	Accuracy
0 - 400.0 Ω	±1% ±3 digits

Open circuit voltage

Continuity beeper sounds @ < 30 Ω

Frequency

Range	Resolution	Accuracy
20 - 400 Hz	1 Hz ±0.1 %	±2 digits
Sensitivity	3 A	

Hold function	Peak Hold: ±3% ±15 digits MIN/MAX : add 15 digits to accuracy for a.c. & d.c. A
Sampling time	10 ms
Positional error	±1% of reading
Overload protection	600 V & 600 A rms
AC conversion type	Average sensing rms indication calibrated to the rms value of a sine wave input
Auto power down	30 minutes after power-on
Display	LCD Display: 3 ½ digit large-scale readout Count: 4000 Sample Rate: 1.5 per second Overrange: "OL"
Battery	1 x 9V PP3 MN1604 6LR61 alkaline cell
Battery life	200 hours (alkaline)
Operating temperature range and humidity	0 °C – 30 °C <80% Rh 30 °C – 40 °C <75% Rh 400 °C – 50 °C <45% Rh
Storage temperature range and humidity	-20 °C – +60 °C (<81% Rh) (batteries removed)
Over-voltage safety category	IEC 61010-1 600V CAT III
Maximum altitude	2000 m
Drop protection	1.2 m onto a hardwood surface
Maximum jaw inner dimensions	35 mm diameter
Calibration accuracy	12 month recommended
Dimensions	68 mm (W) x 237 mm (H) x 42 mm (D)
Weight	225 g including batteries

ORDERING INFORMATION

Description Order Code

DCM340 Digital clampmeter;
600 A ac & dc; 600 V a.c. & d.c.; 400 Ω; 400Hz 1000-305

Included accessories

Batteries

Pouch

Test leads

User guide

Optional accessories

Replacement test leads

Replacement Red/Black Test lead set	1002-001B
Fused Red/Black test lead set	1002-015B

SALES OFFICE

Megger Limited
Archcliffe Road Dover
CT17 9EN England
T +44 (0) 1304 502101
E UKsales@megger.com

DMC340_DS_en_V04

www.megger.com

ISO 9001

The word 'Megger' is a registered trademark

Megger ^R