

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0313872014

Status:


Active

Overview:

MX123 Sealed Connection System

Description:

2.54mm Pitch, MX123 Header, 73 Circuits Shrouded Assembly, (72) 0.64mm Square Signal Pins + (1) 2.8mm Power Blade, Harness Side Key Code A, Black (Au Mate Side Finish)



Documents:	
3D Model	Application Specification AS-31386-200-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-916-001 (PDF)
Drawing (PDF)	Test Summary TS-34566-002-001 (PDF)
Product Specification PS-31387-200-001 (PDF)	Datasheet (PDF)
Product Specification PS-34566-0000-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	31387
Application	Automotive, Power, Wire-to-Board
Component Type	PCB Header
Overview	MX123 Sealed Connection System
Product Name	MX123
Taxonomy	PCB Headers and Receptacles
UPC	822348860661
Physical	
Breakaway	No
Circuits (Loaded)	73
Circuits (maximum)	73
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon Alloy
Net Weight	22.610/g
Number of Rows	4
Orientation	Vertical
PC Tail Length	6.50mm
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	11.0A

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free Status Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series 31387 Series
Mates With MX123 Female Harness Connector Assembly 34566
Use With 33467 MX64 Female Terminals Au

Voltage - Maximum	500V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-31386-200-001
Packaging Specification	PK-31301-916-001
Product Specification	PS-31387-200-001, PS-34566-0000-001
Sales Drawing	SD-31387-073-000, SD-31387-173-000
Test Summary	TS-34566-002-001

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION