



	1	2	3	4
A	Technische Daten / Technical Data			
	Empf. Mindeststrasterabstand / Rec. Center Spacing	2,30 mm		0,0906 inch
	Federkraft / Spring Force	0,8 N		0,8 N
	Vorspannung / Preload	-		-
	Maximaler Federweg / Max. Travel:	2,30 mm		0,0906 inch
	Empfohlener Kontakthub / Recomm. (rated) Travel:	1,50 mm		0,0591 inch
	Temperaturbereich / Temperature Range	-55°C ... +250°C		-67°F ... +482°F
	Typischer Widerstand / Typical Resistance	100 mOhm		100 mOhm
	Typischer Nennstrom / Rated Current Load	3 A		3 A
	E-Maß / Extension Height	8,25 mm		0,3251 inch
B	Werkstoffe / Materials			
	Kolben / Plunger	CuBe, vergoldet		BeCu, gold plated
	Gehäusehülse / Barrel	Neusilber		Nickel silver
	Feder / Spring	Edelstahl, vergoldet		Stainless steel, gold plated



Unless otherwise defined Unit available in: mm/inch		fixtest 		Technical data sheet 				
	Name	Date	Note revision:	Batteriekontakt Battery probe				
Created by	PCh	19.08.2013						
Checked by								
Approved by								
Rev_A								
Rev_B				Drawing number: FK-441				
Rev_C				Material:	Scale:12:1	Change 0	DIN A4	Page 1/1