

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0346910160

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Right-Angle Header Assembly, 16 Circuits, Polarization A, Black, Tray

|                                                              |                                                                     |
|--------------------------------------------------------------|---------------------------------------------------------------------|
| Documents:                                                   |                                                                     |
| <a href="#">3D Model</a>                                     | <a href="#">Application Specification 347290200-AS-CH-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Application Specification AS-34729-020-001 (PDF)</a>    |
| <a href="#">3D Model (PDF)</a>                               | <a href="#">Brochure (PDF)</a>                                      |
| <a href="#">Product Specification PS-34729-020-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>                |

|                |                                                      |
|----------------|------------------------------------------------------|
| General        |                                                      |
| Product Family | PCB Headers                                          |
| Series         | 34691                                                |
| Application    | Automotive, Power, Wire-to-Board                     |
| Comments       | Polarization A                                       |
| Component Type | PCB Header                                           |
| Overview       | Stac64 Single, Multi-Pocket and Hybrid Header System |
| Product Name   | Stac64                                               |
| Taxonomy       | PCB Headers and Receptacles                          |
| UPC            | 800756894324                                         |

|                                |                                |
|--------------------------------|--------------------------------|
| Physical                       |                                |
| Breakaway                      | No                             |
| Circuits (Loaded)              | 16                             |
| Circuits (maximum)             | 16                             |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 10                             |
| First Mate / Last Break        | No                             |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | Yes                            |
| Material - Metal               | Brass                          |
| Material - Plating Mating      | Tin                            |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 7.504/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Right Angle                    |
| PC Tail Length                 | 3.36mm                         |
| PCB Locator                    | Yes                            |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 1.57mm                         |
| Packaging Type                 | Tray                           |
| Pitch - Mating Interface       | 2.54mm                         |
| Pitch - Termination Interface  | 2.54mm                         |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| Shrouded                       | Yes                            |
| Stackable                      | No                             |
| Surface Mount Compatible (SMC) | No                             |
| Temperature Range - Operating  | -40° to +105°C                 |
| Termination Interface: Style   | Through Hole                   |

Electrical



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34691 Series

Mates With

34729 2.54mm (.100") Pitch Stac64 Receptacle Assembly <br> 31408 USCAR 2.54mm (.100") Pitch Receptacle

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 10.0A |
| Voltage - Maximum             | 500V  |

**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 040  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 003  |
| Process Temperature max. C                     | 260  |

**Material Info**

**Reference - Drawing Numbers**

|                           |                                       |
|---------------------------|---------------------------------------|
| Application Specification | 347290200-AS-CH-000, AS-34729-020-001 |
| Product Specification     | PS-34729-020-001                      |
| Sales Drawing             | SD-34691-100-001                      |

This document was generated on 01/04/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**