

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347290201

Status:


Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Receptacle Housing, 20 Circuits, Dual Row, Polarization B, Gray, Tray



Documents:	
3D Model (PDF)	Application Specification AS-34729-020-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-201-001 (PDF)
3D Model	Brochure (PDF)
Product Specification PS-34729-020-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 347290200-AS-CH-000 (PDF)	
General	
Product Family	Crimp Housings
Series	34729
Application	Automotive, Signal, Wire-to-Board
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Polarization	B
Product Name	Stac64
Taxonomy	Connector Housings
UPC	884982006553
Physical	
Circuits (maximum)	20
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Net Weight	7.530/g
Number of Rows	2
Packaging Type	Tray
Panel Mount	N/A
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	10.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	347290200-AS-CH-000, AS-34729-020-001
Packaging Specification	PK-31301-201-001
Product Specification	PS-34729-020-001
Sales Drawing	SD-34729-020-001

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS
ELV
RoHS Phthalates

Green Image
Compliant
Not Contained

Search Parts in this Series
34729 Series

Mates With
34690 2.54mm Pitch Stac64 Vertical Header, 34691 2.54mm Pitch Stac64 Right Angle Header

Use With
34803 CTX64 Female Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION