

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349002120

Status:

Active

Overview:

MXP120 Sealed Connector System

Description:

MXP120 Sealed Receptacle, 2 Circuit, Black Housing (T3-V2-S3 /T4-V4-S3), Key A, Black Insert



Documents:	
3D Model	Application Specification AS-34900-0001-CH-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-898-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Application Specification AS-34900-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link	
Application Tooling Part Link	63824-6300
General	
Product Family	Crimp Housings
Series	34900
Application	Automotive, Body Electronics, Power Train, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	MXP120 Sealed Connector System
Polarization	A
Product Name	MXP120 Sealed
Taxonomy	Connector Housings
UPC	889056197618
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	2.577/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +155°C
Electrical	
Current - Maximum per Contact	13.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-34900-0001-001, AS-34900-0001-CH-001
Packaging Specification	PK-31301-898-001
Sales Drawing	PS-34900-0001-001, SD-34900-2001-001, SD-34900-6001-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34900 Series

Mates With

MXP120 Male Blade Connector [34899](#)

Use With

MXP120 Backshell [1600912010](#) , [1600912110](#) , [1600912210](#)
MXP120 Cavity Plug [349961501](#)
MXP120 Cavity Plug Seal [349961902](#)
1.2 LL SWS from Tyco and Kostal

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Toolkit for MXP120 Sealed Connection System	638246300

This document was generated on 10/12/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION