

IN180250**INDUCTIVE SENSORS • INCREASED AMBIENT TEMPERATURE**

sensor inductive, M18x1 78long, Non-flush, Sn: 8, 10-35V DC, 180°C,
PNP NC, Cable 2m Silicone, IP50, Stainless steel 1.4305

**MECHANICAL FEATURES**

Alignment of cable entry	Axial
Ambient temperature	0 °C ... 180 °C
Cable infeed	Axial
Cable length	2 m
Degree of protection (IP)	IP50
Design	Cylinder, screw-thread
Housing material	Stainless steel 1.4305
Increased ambient temperatures > 80°C	+
Material of cable sheath	Silicone
Mechanical mounting condition for sensor	Non-flush
Pressure-proof	-
Sensor length	78 mm
Thread pitch	1 mm
Thread size, metric	18
Wire cross section	0.25 mm ²

ELECTRICAL FEATURES

Cascadable	-
Rated switching current	150 mA
Readiness delay	5 ms
Relative repeat accuracy	3 %
Residual ripple	10 %
Response time	1.2 ms
Reverse polarity protection	+
Short-circuit protection	+
Suitable for safety functions	-
Supply voltage	10 V ... 35 V
Switching distance	8 mm
Switching frequency	200 Hz
Type of electrical connection	Cable
Type of switching function	Normally closed contact
Type of switching output	PNP
Voltage drop	2 V


ELECTRICAL FEATURES

Voltage type	DC
With monitoring function of downstream devices	-
Other	
Packaging dimensions	77.0mm x 25.0mm x 123.0mm
Shipping weight	0.14kg
Tariff code	85365019


Classification

ipf product group	202
eClass 8.0	27270101
eClass 9.0	27270101
eClass 9.1	27270101
ETIM-5.0	EC002714
ETIM-6.0	EC002714
ETIM-7.0	EC002714

Connection



Dimensional drawing



Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.

