

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0541044031

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 40 Circuits, Gold Plating



Series image - Reference only

Documents:	
Drawing (PDF)	Packaging Specification SPK-54104-001-001 (PDF)
2D Drawing (DXF)	Datasheet (PDF)
3D Model (PDF)	Product Guide (PDF)
2D Drawing DXF (PDF)	RoHS Certificate of Compliance (PDF)
3D Model	Reference Guide (PDF)
Product Specification PS-54104-071-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	54104
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
Taxonomy	FFC / FPC Connectors
UPC	822348532391
Physical	
Actuator Type	Slider
Circuits (Loaded)	40
Color - Resin	Natural
Contact Position	Top
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	2.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	454.480/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Material Info	

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free Status Not Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
54104 Series

Mates With
Premo-Flex FFC Cable 15020

Reference - Drawing Numbers

Packaging Specification	SPK-54104-001-001
Product Specification	PS-54104-071-001
Sales Drawing	541040000-000, 541041000-000

This document was generated on 01/04/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION