

PG800570
LASER SENSORS • FORKED LIGHT BARRIER

sensor laser, fork, 100x10x80mm, fork width 80mm, 10-30V DC, 1x PNP/NPN NC/NO, Connector M8 3pin, IP67, Zinc die-cast+Glass, Red light, 5kHz pulsed, Manual adjustment


MECHANICAL FEATURES

Ambient temperature	-25 °C ... 60 °C
Degree of protection (IP)	IP67
Design	Cuboid
Diameter detection	-
Fork depth	55 mm
Fork light barrier design	Furcate
Fork width	80 mm
Housing material	Zinc die-cast
Installation bracket	-
Material of optical surface	Glass
Sensor height	100 mm
Sensor length	10 mm
Sensor width	80 mm

ELECTRICAL FEATURES

Analog output 0 V ... 10 V	-
Analog output 4 mA ... 20 mA	-
Connection to amplifier	-
Decay time	0.1 ms
Dynamic switching output	-
Equipment protection class	Protection class 3
No-load current	30 mA
Number of pins	3
Number of switching outputs	1
Operating voltage	10 V ... 30 V
Rated switching current	100 mA
Relative repeat accuracy	0.01 mm
Repeatability +/-	10 µm
Response time	0.1 ms
Reverse polarity protection	+
Scanning function	Light-/dark-on mode
Setting procedure	Manual adjustment
Short-circuit protection	+

ELECTRICAL FEATURES

Switching frequency	5000 Hz
Type of electrical connection	Connector M8
Type of switching function	Normally closed contact/normally open contact
Type of switching output	PNP/NPN
Type of the forked light barrier	Standard
Voltage drop	2 V
Voltage type	DC
With communication interface, analog	-
With communication interface, RS-232	-
With other analog output	-
With time function	-

OPTICAL FEATURES

Min. object size	0.05 mm
Resolution	50 µm
Light beam form	Point
Laser class	Class 1
Pulsed light source	+

OTHER FEATURES

Feeding technology	+
--------------------	---


Other

Packaging dimensions	150mm x 10mm x 160mm
Shipping weight	
Tariff code	85365019

Classification

ipf product group	170
eClass 8.0	27270909
eClass 9.0	27270909
eClass 9.1	27270909
ETIM-5.0	EC002720
ETIM-6.0	EC002720
ETIM-7.0	EC002720

Connection

Dimensional drawing**Installation**

Mounting / installation may only be carried out by a qualified electrician!

Disposal**Safety warnings**

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information.

Never use these devices in applications where the safety of a person depends on their functionality.

LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.