

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5601230600

Status:

Active

Overview:

DuraClik Connector System

Description:

DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, White, 6 Circuits

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-560123-001-001 (PDF)

Product Specification PS-560123-003-001 (PDF)

Application Specification AS-560123-001-001 (PDF)

Packaging Specification PK-560123-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

560123

Automotive, Signal, Wire-to-Board

DuraClik Connector System

DuraClik

Connector Housings

889056009546

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

6

White

Receptacle

No

None

Yes

PBT

0.373/g

1

Bag

No

2.00mm

Yes

No

-40° to +130°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

AS-560123-001-001

PK-560123-001-001

PS-560123-001-001, PS-560123-003-001

SD-560123-004-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

560123 Series

Mates With

DuraClik Right-Angle Header [502352](#)
DuraClik Vertical Header [560020](#)

Use With

DuraClik ISL Terminal [560124](#)
DuraClik ISL Retainer [5601250600](#) , [5601250601](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION