

# Ultra-Light & Long Combination Wrench & Set

KT No. & D1






1061

**PAT.**




**TAIWAN**  
EXCELLENCE 2016

- New forge technologies I-Beam shank offers 20% lightweight and better strength
- 15° open slimline type
- 13° ring end offset from shaft
- Chrome vanadium alloy steel
- Chrome plated
- DIN 3113 from A / ISO 7738



| KT NO.  | Size mm | L mm | g   | kg       |
|---------|---------|------|-----|----------|
| 1061-06 | 6       | 128  | 19  | 12 / 768 |
| 1061-07 | 7       | 148  | 31  | 12 / 576 |
| 1061-08 | 8       | 148  | 29  | 12 / 576 |
| 1061-09 | 9       | 167  | 46  | 12 / 384 |
| 1061-10 | 10      | 167  | 47  | 12 / 384 |
| 1061-11 | 11      | 186  | 58  | 12 / 240 |
| 1061-12 | 12      | 196  | 62  | 12 / 192 |
| 1061-13 | 13      | 205  | 85  | 12 / 192 |
| 1061-14 | 14      | 223  | 101 | 12 / 120 |
| 1061-15 | 15      | 233  | 121 | 12 / 144 |
| 1061-16 | 16      | 243  | 135 | 12 / 144 |
| 1061-17 | 17      | 262  | 168 | 12 / 96  |
| 1061-18 | 18      | 272  | 187 | 12 / 96  |

| KT NO.  | Size mm | L mm | g   | kg      |
|---------|---------|------|-----|---------|
| 1061-19 | 19      | 281  | 203 | 12 / 96 |
| 1061-20 | 20      | 301  | 273 | 8 / 48  |
| 1061-21 | 21      | 301  | 269 | 8 / 48  |
| 1061-22 | 22      | 319  | 304 | 8 / 48  |
| 1061-23 | 23      | 319  | 301 | 8 / 48  |
| 1061-24 | 24      | 338  | 370 | 5 / 40  |
| 1061-25 | 25      | 358  | 450 | 5 / 40  |
| 1061-26 | 26      | 358  | 431 | 5 / 40  |
| 1061-27 | 27      | 383  | 510 | 5 / 40  |
| 1061-28 | 28      | 383  | 508 | 5 / 40  |
| 1061-29 | 29      | 408  | 617 | 5 / 20  |
| 1061-30 | 30      | 408  | 599 | 5 / 20  |
| 1061-32 | 32      | 433  | 789 | 5 / 20  |



► Pouch material : Teton

| KT NO.    | PC. | Contents                                                                                     | kg   | kg     |
|-----------|-----|----------------------------------------------------------------------------------------------|------|--------|
| 12C7MRN   | 7   | 8, 10, 11, 13, 14, 17, 19                                                                    | 0.77 | 1 / 24 |
| 12C7MRN01 | 7   | 8, 10, 12, 13, 14, 17, 19                                                                    | 0.77 | 1 / 24 |
| 12C8MRN   | 8   | 6, 7, 8, 9, 10, 11, 12, 13                                                                   | 0.77 | 1 / 24 |
| 12A0MRN   | 10  | 10, 11, 12, 13, 14, 15, 16, 17, 18, 19                                                       | 1.35 | 1 / 12 |
| 12A1MRN   | 11  | 8, 10, 12, 13, 14, 16, 17, 18, 19, 22, 24                                                    | 2.06 | 1 / 12 |
| 12A3MRN   | 13  | 8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 22, 24                                            | 2.16 | 1 / 12 |
| 12A4MRN   | 14  | 8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24                                        | 2.44 | 1 / 8  |
| 12B4MRN   | 24  | 6, 8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30, 32 | 7    | 1 / 2  |



1061



WRENCHES