

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0743204000

Status:


Active

Overview:

MicroCross DVI Connectors and Cable Assemblies

Description:

MicroCross DVI-D Digital Visual Interface, PCB Receptacle, Panel Mount, Polyester (PCT), Through Hole, 2.34mm PC Tail Length, Right-Angle, 0.76µm Gold (Au), Lead-Free, Screw Hole, 24 Circuits



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-74320-001-001 (PDF)

Product Specification TS-74320-001-001 (PDF)

Packaging Specification PK-74320-010-002 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Component Type

Electrical Model

Overview

Product Name

Taxonomy

Type

UPC

I/O Connectors

74320

Wire-to-Board

DDWG (Digital Display Working Group) Standard

Receptacle

Yes

MicroCross DVI Connectors and Cable Assemblies

MicroCross DVI

I/O Connectors

N/A

800754009980

Physical

Boot Color

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Gender

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Ports

N/A

24

24

Natural

100

94V-0

Receptacle

Yes

Yes

Copper Alloy

Gold

Tin

6.630/g

3

Right Angle

2.34mm

Yes

Yes

Tray

Yes

1.90mm

1.90mm

0.762µm

2.540µm

Yes

Yes

1

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

74320 Series

Mates With

88744 , 74323

Use With

Hex Screw Kit 717811000 or 717812000

Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20° to +85°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	3.0A
Grounding to Panel	Yes
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	40V AC (RMS)
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Electrical Model Document	EE-74320-001-001
Packaging Specification	PK-74320-010-002
Product Specification	PS-74320-001-001, TS-74320-001-001
S-Parameter Model	SP-74320-001-001
Sales Drawing	SD-74320-003-000

This document was generated on 10/25/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION