

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0878321414

Status:

Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Vertical, Surface Mount, Shrouded, Lead-Free, 14 Circuits, 0.38µm Gold (Au) Plating, with Locking Windows, with Center Polarization Slot, with Cap, without PCB Locator, Tape and Reel

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-87831-027-001 (PDF)

Application Specification 503940001-AS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Component Type

Overview

Product Name

Taxonomy

UPC

PCB Headers

87832

Signal, Wire-to-Board

PCB Header

Milli-Grid Connector System

Milli-Grid

PCB Headers and Receptacles

883906685980

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

No

14

14

Black

100

No

94V-0

No

No

Yes

Yes

Phosphor Bronze

Gold

Tin

Nylon

0.698/g

2

Vertical

No

None

Tube

2.00mm

2.00mm

0.381µm

1.905µm

No

Fully

No

Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

87832 Series

Mates With

Milli-Grid Vertical Through Hole Receptacle

79107 , 78787 , Milli-Grid Flex-to-Board

Vertical Receptacle 79108 , Milli-Grid

Vertical Surface Mount Receptacle 79109

, 78788 , Milli-Grid Crimp Housing 51110 ,

Milli-Grid Cable-to-Board Receptacle 87568

Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	125V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	503940001-AS-000
Product Specification	PS-87831-027-001
Sales Drawing	SD-87832-0001-001

This document was generated on 01/20/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION