

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0988171020

Status:

Active

Overview:

NSCC - New Standard Casing Contact

Description:

NSCC Single Part, Unsealed, 1.50mm, Female Housing, 3.33mm Pitch NSCC, Wire-to-Wire, 2 Circuits, White

Documents:

3D Model

Application Specification 988210001-PS-CH-001 (PDF)

Drawing (PDF)

Packaging Specification PK-31301-635-001 (PDF)

Product Specification PS-98821-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Application Specification 988210001-AS-CH-001 (PDF)

Application tooling part link

Application Tooling Part Link

63813-3800

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

98817

Power, Wire-to-Wire

NSCC - New Standard Casing Contact

NSCC

Connector Housings

822348761340

Physical

Breakaway

Circuits (maximum)

Circuits Detail

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Ports

Temperature Range - Operating

No

2

2 x 1.5mm female terminals

White

Receptacle

No

Yes

Yes

Polyester

1.790/g

1

Carton

No

3.33mm

3.33mm

Yes

1

-40° to +100°C

Electrical

Current - Maximum per Contact

10.0A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

010009329

Reference - Drawing Numbers

Application Specification

Packaging Specification

988210001-AS-CH-001, 988210001-PS-CH-001

PK-31301-635-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

98817 Series

Mates With

988221020 Male Receptacle Housing

Use With

Female Terminal NSCC 988971109 , 988971119 , 988971129 or FCI Female Terminal 1.5 Sicma 3

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extractor Tool for Unsealed Receptacle Connectors

638133800

This document was generated on 01/18/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION