

YASKAWA

GA700

AC Drives for Industrial Applications



Limitless Possibilities

Incredibly reliable, easy to use, and powerful!

At YASKAWA, we know your time is valuable. That's why we've designed this variable speed drive to meet all your needs. Offering world class YASKAWA quality, along with intuitive interaction and high flexibility, our new GA700 is meant to easily handle nearly any application.

Discover the limitless possibilities of GA700!



With a flexible motor control, powerful and extendable functionality, and a broad power range up to 355 kW, the GA700 is the drive of choice for almost any task, ranging from simple transportation, presses and others up to complex systems with network connected drives or the demand for higher levels of safety.

Equally impressive to its robust, powerful and flexible design are innovative features like the tuning-less vector control, the haptic keypad with guided configuration and DriveWizard Mobile, the app for smart phones and tablets.

Combine all this with modern safety features and a variety of environmental solutions, and you will need to look no further than GA700 for all your variable speed needs.

Our Commitment to You

Effortless network integration

- Supports all major networks with a new cost effective network integration feature
- Maintain network communications even during loss of main input power

One for all

- Precise and tuning-less motor control with one drive controlling any induction, permanent magnet or synchronous reluctance motor

Quick & easy set-up

- Reduce set-up time with an intuitive keypad, navigation and start-up wizards

Powerful configuration tools

- DriveWizard® and DriveWorksEZ® are PC tools for drive management and logic programming
- DriveWizard® for drive management, start-up and failure analysis
- DriveWorksEZ® for extending functionality by logic programming

Convenient set-up and monitoring

- Safe programming without main power connected
- Cloud-connected DriveWizard® Mobile app for drive management on smartphones and tablets.

Integrated functional safety

- Increased safety and reliability with STO SIL3 functional safety

Meets global standards

- Local/global standards
- RoHS compliant

Flexible package design

- Designed with flexibility to simplify installation and cabinet design


Flexibility, ease of use and a sustainable design for the best value proposition in your application



200 V class: 0.55 - 110 kW
400 V class: 0.55 - 355 kW

Effortless Network Integration

GA700 drives support all the major industrial communications and connection topologies (ring, star, line, etc.) to adapt to various factory automation networks. Reduce wiring when connecting to an upper level controller or PLC through available built-in protocols and/or dedicated communication options.



Network integration benefits/features:

Easy integration into your network

- Supports all major networks and topologies
- Network compliance tested
- Network up to 5 drives with a single communication card

Cost savings with built-in protocols

- RS-485 MEMOBUS/Modbus protocol
- 115.2 kbit/s communication speeds

Keep control during main power loss

- Embedded +24 VDC input control power standard
- Programming and monitoring without main power

Cost effective integration

Up to five GA700 drives can be accessed through only one fieldbus option card, thus providing a cost effective solution with reduced wiring effort.

Embedded +24 VDC input

When supplying the GA700 through the built in 24 VDC control power input, network communications can be maintained even during main power loss, thus allowing continuous monitoring and faster start up on power recovery.



DeviceNet™ EtherNet/IP™

EtherCAT®

ETHERNET
POWERLINK

CC-Link

CANopen®

Modbus

MECHATROLINK


PROFI
NET

PROFI
BUS

One For All



The GA700 precisely controls induction motors, permanent magnet motors and synchronous reluctance motors providing versatility to run a variety of applications with just one drive. The times of complex motor set-up are over. With the new EZ vector mode, the GA700 can run all of these motor types without comprehensive tuning.




Motor control benefits and features:

Flexible motor control

- Tuning-less with EZ vector
- Open/closed loop speed or torque control
- Induction/permanent magnet motors
- 590 Hz max. output frequency
- Zero speed control without encoder
- Synchronous reluctance motor control
- Motor speed control range in closed loop mode of 1:1500

Energy savings

- Automatic energy efficiency optimization function



Maximum efficiency

By introducing motor speed control as a replacement of gears, valves or dampers the GA700 unlocks great energy saving potential in various applications. In addition, the GA700 automatically optimizes the motor efficiency for any speed and load condition and minimizes overall losses.

GA700 lowers energy cost by running your application at maximum efficiency.

Quick & Easy Set-up

The GA700 provides a user programming experience with an intuitively-designed keypad and tactile user interface. Self-guiding navigation menus and start-up wizards make the programming and set-up faster and easier than ever. With DriveWizard Mobile the GA700 can easily be managed and controlled from your smartphone or tablet.

Mobile Device Connectivity

Mobile device connectivity is achieved through using the built-in USB port or wireless communication with the Bluetooth® LCD keypad option.



1. Bluetooth keypad optional
2. Supports Android and iOS



Copy function

Multiple sets of parameters can be stored and easily transferred (copied) to additional drives

Hi-resolution display

Contrast control offers clear and readable full-text descriptions

Automatic backup function

Saves the current parameter settings after a period of user inactivity. After an incident, settings can be retrieved from the keypad in a couple of seconds.

Advanced keypad navigation

Faster scrolling and function keys offer faster navigation and short-cuts reducing program-time



Micro SD storage

Micro SD for data logging storage

Real-time clock

Real-time clock for time stamp of fault information (battery compartment in back)

Optional LCD keypad with Bluetooth®

Wireless communication capability between the mobile device and drive

Keypad benefits and features:

Reduce set-up time

- Start-up wizard
- Favorite parameter/monitor function
- Copy function integrated into the keypad
- Parameter set is backward compatible with previous generation drive products
- Fast navigation
- Parameter description

Drive parameter management

- Storage of up to 4 drive parameter sets
- Data logging with real time stamp e.g. for fault analysis, load profile analysis etc. (up to 32 GB on a Micro SD card)
- Fault logging with real time stamp for better analysis
- Multiple parameter storage
- Automatic parameter back-up

Easy to use

- LCD keypad with Bluetooth® option
- Display contrast control
- Real-time clock with time stamp
- Tactile feel buttons
- Remote mounting of keypad using standard RJ45 extension cable


Start-up wizard

Reduce basic set-up time to minutes using the start-up wizard without any drive parameter knowledge



Powerful Configuration Tools

DriveWizard® is an offline/online parameter and drive configuration tool. The easy and intuitive tool is used for set-up, maintenance and troubleshooting offering parameter editing, storing and file comparison as well as online trending using the highly functional oscilloscope feature.



Easy commissioning without power


GA700 can be programmed without any power supply connected. Simply plug into a USB port of your PC, start programming and enjoy the ease of commissioning.



Customizable



The GA700 further enhances the programming experience with DriveWorksEZ®. DriveWorksEZ® offers an icon-based, drag-and-drop graphical environment to add programmable functions that can tailor the drive to meet various machine and application requirements without the cost of external controllers, such as PLCs or additional controller hardware options.



 DriveWorksEZ

Application toolbox benefits and features:

Drive management with DriveWizard®

- Parameter management
- Online manual
- Report generation and export data
- 6 channel scope function
- Real-time monitoring
- Access through USB, EtherNet/IP, Modbus TCP/IP, or PROFINET
- Automatic parameter conversion from previous series drives

Customizable with DriveWorksEZ®

- Icon-based graphics
- Drag and drop graphical interface
- Select from 300+ function blocks
- Access to I/Os, network interfaces, drive parameters and monitors
- Logic/math functions
- Timers/counters
- Subroutine creation
- Up to 200 connections

Easy programming

DriveWorksEZ® is the intuitive graphical programming environment for the GA700. Create customized functions for your application in shortest time by drag and drop function blocks. The online diagnosis tool supports testing.



Convenient Set-up And Monitoring

Using DriveWizard Mobile the GA700 can be set up, controlled and monitored from your smartphone or tablet easily and intuitively. Connected with the YASKAWA Drive Cloud, DriveWizard Mobile provides quick access to latest product manuals and your drive data, anywhere and anytime.

DriveWizard® Mobile app

DriveWizard® Mobile turns your smartphone or tablet into a control center for your GA700 drives. It allows parameter setup and drive control but also back up your drive data locally on your smart device or in the YASKAWA Drive Cloud. With DriveWizard® Mobile all your information for parameter setup and troubleshooting of your GA700 drives are in your pocket when you need them.

Scanning the drive QR code can provide easy access to drive information and status with the DriveWizard Mobile application software.





YASKAWA Drive Cloud service

With the YASKAWA Drive Cloud, we provide free drive registration access to latest product information and online storage for parameter and application backup data. YASKAWA Drive Cloud is the easy and safe way to keep a record of your drive data and to have them available whenever you need them.



Convenient setup and monitoring:

DriveWizard® Mobile app

- Quick and easy drive management apps for smart devices
- Easy USB OTG cable or Bluetooth® connection
- Drive registration via cloud by scanning QR code
- Paperless and easy access to latest online manual and troubleshooting
- Archive and retrieve parameter settings with comments on your smart device
- Carefree data recovery: Parameter back-up/retrieval anytime via cloud service for registered drives

YASKAWA Drive Cloud service

- Online manual
- Complimentary storage for parameter backup and application records
- Convenient drive data storage accessible anywhere
- Direct access to your personal GA700 data package

Search for

YASKAWA

on



Flexible And Reliable

No matter if you put the drive in a control cabinet or at a wall, in clean or harsh environment, the flexible package design of the GA700 allows a reliable operation under various environmental conditions.



Minimum footprint


The small footprint of the GA700 provides best usage of available panel space. Optimized heat management results in an up to 50% smaller footprint compared to previous drives.



Coated board protection

Coated PCBs as standard protect the electronics from dust or humidity and ensure reliable operation even in a harsh environment (IEC 60723-3-3, 3C2, 3S2).





Side-by-side mounting

The GA700 can be mounted side-by-side with bottom entry wiring to reduce cabinet size.

Enhanced product benefits and features:

Easy to install and maintain

- IP20 standard
- NEMA Type 1 kit optional
- NEMA Type 12/IP55 protected heatsink
- Coated boards
- Side-by-side mounting
- Built-in braking transistor (up to 90 kW)

Reduce harmonics and emissions

- Built-in EMC filter, possible to disable
- Built-in DC reactor (22 kW (HD) and above)



Easy external back heatsink mounting

The GA700 with a integrated flange design offers easy installation when mounting the heatsink outside the cabinet to reduce cabinet size and cooling equipment. In addition, the factory optional Type 12/IP55 heatsink design can provide greater protection from dust particles while reducing cooling requirements resulting in smaller cabinets.

Mounting for external heatsink



Horizontal mounting

The GA700 can be mounted horizontally up to 90 kW (ND).





Integrated Functional Safety

With the built-in dual channel STO (safe torque off) circuit and EDM signal (electronic device monitor


Specifications

Operating Environment	
Ambient temperature	-10 to +50 °C (IP20), -10 to +40 °C (NEMA 1), up to

Specification Overview


Motor Control		
Motor types	Induction Motor (IM), Permanent Magnet Motor (IPM/SPM), Synchronous Reluct	

Connection Diagram



Technical Data

Catalog Code



Ratings

200 - 240 VAC, 3-Phase

Catalog Code GA70C□□□□BA	Max Applicable Motor Power	Rated Output Current	Dimensions [mm]			Weight [kg]
	HD / ND [kW]	HD / ND [A]	Height	Width	Depth	
2004	0.55 / 0.75	3.2 / 3.5	260	140	176	3.5
2006	0.75 / 1.1	5.0 / 6.0				
2010	1.5 / 2.2	8.0 / 9.6				
2012	2.2 / 3.0	11 / 12.2			211	3.9
2018	3.0 / 4.0	14 / 17.5				
2021	4.0 / 5.5	17.5 / 21				4.2
2030	5.5 / 7.5	25 / 30				
2042	7.5 / 11	33 / 42	300	180	202	6.0
2056	11 / 15	47 / 56	350	220	227	8.5
2070	15 / 18.5	60 / 70				9.0
2082	18.5 / 22	75 / 82	400	240	280	20
2110	22 / 30	88 / 110				35
2138	30 / 37	115 / 138				40
2169	37 / 45	145 / 169	543	264	335	40
2211	45 / 55	180 / 211				
2257	55 / 75	215 / 257	700	312	420	80
2313	75 / 90	283 / 313				
2360	90 / 110	346 / 360	800	440	472	120
2415	110 / -	415 / -				



Ratings

380 - 480 VAC, 3-Phase

Catalog Code GA70C□□□□BA	≤ 380 to 460 VAC		> 460 VAC		Dimensions [mm]			Weight [kg]
	Max Applica- ble Motor	Rated Output Current	Max Applica- ble Motor	Rated Output Current	H	W	D	
	HD / ND [kW]	HD / ND [A]	HD / ND [kW]	HD / ND [A]				
4002	0.55 / 0.75	1.8 / 2.1	0.55 / 0.75	1.6 / 2.1	260	140	176	3.5
4004	0.75 / 1.5	3.4 / 4.1	0.75 / 1.5	2.1 / 3				
4005	1.5 / 2.2	4.8 / 5.4	1.5 / 2.2	3.4 / 4.8				
4007	2.2 / 3.0	5.5 / 7.1	2.2 / 3.0	4.8 / 6.9				
4009	3.0 / 3.7	7.2 / 8.9	3.0 / 3.7	6.9 / 7.6				
4012	3.7 / 5.5	9.2 / 11.9	3.7 / 5.5	7.6 / 11				
4018	5.5 / 7.5	14.8 / 17.5	5.5 / 7.5	11 / 14				
4023	7.5 / 11	18 / 23.4	7.5 / 11	14 / 21				
4031	11 / 15	24 / 31	11 / 15	21 / 27	300	180	202	6.0
4038	15 / 18.5	31 / 38	15 / 18.5	27 / 34	350	220	227	7.5
4044	18.5 / 22	39 / 44	18.5 / 22	34 / 40			246	13
4060	22 / 30	45 / 59.6	22 / 30	40 / 52	400	240	280	16
4075	30 / 37	60 / 74.9	30 / 37	52 / 65	450	255		35
4089	37 / 45	75 / 89.2	37 / 45	65 / 77				
4103	45 / 55	91 / 103	45 / 55	77 / 96	543	264	335	40
4140	55 / 75	112 / 140	55 / 75	96 / 124				
4168	75 / 90	150 / 168	75 / 90	124 / 156	700	312	420	80
4208	90 / 110	180 / 208	90 / 110	156 / 180				
4250	110 / 132	216 / 250	110 / 150	180 / 240				
4296	132 / 160	260 / 296	150 / 185	240 / 302	800	440	472	120
4371	160 / 200	304 / 371	185 / 220	302 / 361				
4389	200 / 220	371 / 389	220 / 260	361 / 414				
4453	220 / 250	414 / 453	260 / 300	414 / 477	1140	510	480	175
4568	250 / 315	453 / 568	300 / 335	477 / 515				
4675	315 / 355	605 / 675	335 / 370	515 / 605				

YASKAWA Europe GmbH

Hauptstr. 185
65760 Eschborn
Germany

+49 6196 569-500
support@yaskawa.eu.com
www.yaskawa.eu.com

08/2019
YEU_INV_GA700_EN_v6

Specifications are subject to change without notice for ongoing product modifications and improvements. © YASKAWA Europe GmbH. All rights reserved.

YASKAWA