









RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REF. ONLY.
4. FUNCTION: SPST
5. RATING: 50mA @ 32VDC
- ▲ 6. OPERATING FORCE: $160 \pm 50\text{gf}$
7. TRAVEL: 0.3 mm
8. CONTACT RESISTANCE: 100 m Ω MAX
- ▲ 9. CONTACT MATERIAL: SILVER
10. DIELECTRIC STRENGTH: 250VAC for 1 min
11. INSULATION RESISTANCE: 10 MEGA Ω min, @ 100VDC
12. ELECTRICAL LIFE: 5,000,000 CYCLES
13. ▲ DENOTES CRITICAL PARAMETER
14. OPERATING TEMP: -40°C to 85°C
15. PACKAGING: TAPE & REEL 1000 PCS

▲ ACTUATOR
COLOR: BROWN

E-SWITCH®

A	24619	NEW RELEASE	12/1/20	JM
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL6150BF160QG

SCALE
5:1DATE
12/1/2020DR
JMDWG
N615004REV
A