









SLIDE SWITCH MODEL SL14
RATING:12A 125/250VAC (cURus)
10A 125/250VAC 6E3(CQC)
8(2)A 125/250V~ 1T85/55 1E4(cURus/ENEC 15)
CONTACT RESISTANCE: 20mΩ INITIAL (MAX)
INSULATION RESISTANCE:DC 500V 100MΩ(MIN)
DIELECTRIC STRENGTH:1,000VAC FOR 1 MINUTE



NOTE:TOLERANCES UNLESS OTHERWISE SPECIFIED:±.012/0.3(in/mm).



REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE 1/2°		UNIT	PART NAME	SL14 SPEC DRAWING	DWG NO
△			DRAWN BY	周俊	DESIGNED BY	周俊	SCALE	3/2		
△			CHECKED BY	周俊	APPROVED BY	周俊	DATE	2023.04.20	SL14-22AM(1A)NC	S9274A
△	2023.04.20	首次出圖		周俊						