






NOTE :-

- 1) ALL EDGES ARE BURR FREE
- 2) NON DIMENSIONAL RADIUS - 2..3mm
- 3) TOLERANCE AS PER DIN ISO 2768-cL
- 4) ALL CORNERS ARE FILLET WELDED AND GRINDED (240 GRAINS)
- 5) FINISH - RAL GRAY 7001 STRUCTURED

Sr No.	Material	UOM	Qty	NO.	REV.NO.	DESCRIPTION	DATE	DRAWN	CHECKED
1	Base Assembly		1						
1.1	Base	Nos	1						
1.2	Din Rail Mounting Channel	Nos	2						
1.3	Blind NutSert M5 - SS 304 (Large Flanged)	Nos	4						
1.4	Bottom Sealing Cap	Nos	4						
2	Lid Assembly		1						
2.1	Lid	Nos	1						
2.2	Sealing Gasket	m	1.04						
2.3	Plastics Insert for Screw	Nos	4						
2.4	Stud EN ISO 13918-PTM6x12- A2-50 - SS 304	Nos	1						
2.5	Oval Head Screw DIN 966 -M5x33- SS 304	Nos	4						

NO.	REV.NO.	DESCRIPTION	DATE	SIGN	NAME	CHECKED
		TITLE :- JUNCTION BOX ASSEMBLY 400 x 150 x 81				
		MATERIAL GI STEEL 1.5mm Thick				
		FINISH Powder Coated Grey RAL 7001				
			01/04/15		MANOJ	DRAWN
			01/04/15		A.M.	CHECKED
					M.S.	APPROVED

SCALE	PARTNO.	DRG. NO.
REV 00	GIJB13-A	