

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022052061

Status:

Active

Overview:

[KK Interconnect Systems](#)

Description:

KK 254 Wire-to-Board Header, Single Row, Right-Angle, 6 Circuits, PA Polyamide Nylon, Tin (Sn) Plating



Series image - Reference only

- Documents:

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[3D Model](#)

[Product Specification PS-10-07-001 \(PDF\)](#)

[Packaging Specification PK-4094-001-001 \(PDF\)](#)

[Symbol Footprint Data SYM-22-05-2061-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Headers
Series		4094
Application		Board-to-Board, Signal, Wire-to-Board
Component Type		PCB Header
Overview		KK Interconnect Systems
Product Name		KK 254
Taxonomy		PCB Headers and Receptacles
UPC		800753755680

Physical		
Breakaway		No
Circuits (Loaded)		6
Circuits (maximum)		6
Color - Resin		Natural (White)
Durability (mating cycles max)		25
Flammability		94V-0
Glow-Wire Capable		No
Lock to Mating Part		None
Material - Metal		Brass
Material - Plating Mating		Tin
Material - Plating Termination		Tin
Material - Resin		Nylon
Net Weight		0.484/g
Number of Rows		1
Orientation		Right Angle
PC Tail Length		3.15mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		1.60mm
Packaging Type		Bag
Pitch - Mating Interface		2.54mm
Pitch - Termination Interface		2.54mm
Plating min - Mating		5.080µm
Plating min - Termination		5.080µm
Polarized to Mating Part		No
Polarized to PCB		No
Shrouded		No
Stackable		Yes
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		See Product Specification

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

4094 Series

Mates With

2695 , 6471 , 7880 , 4455 , 7720

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	A-4094-06A197
Reference - Drawing Numbers	
Packaging Specification	PK-4094-001-001
Product Specification	PS-10-07-001
Sales Drawing	SDA-4094-001
Symbol/Footprint Data	SYM-22-05-2061-001

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION