

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0310671010

Status:

Active

Overview:

H-DAC 64 Unsealed Connector System

Description:

2.54mm H-DAC 64, 3 Way Receptacle Assembly, Single Row, Polarization A

Documents:

3D Model

Application Specification AS-31067-100-001 (PDF)

Drawing (PDF)

Packaging Specification PK-30907-737-001 (PDF)

3D Model (PDF)

Packaging Specification PK-31301-076-001 (PDF)

Product Specification PS-31100-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Crimp Housings

Series

31067

Application

Automotive, Power, Wire-to-Board, Wire-to-Wire

Comments

Polarization Option A, Black

Overview

H-DAC 64 Unsealed Connector System

Product Name

H-DAC 64

Taxonomy

Connector Housings

UPC

800756063041

Physical

Circuits (maximum)

3

Color - Resin

Black, White

Gender

Receptacle

Glow-Wire Capable

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Modified Polystyrene, Polyester

Net Weight

1.100/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Polarized to Mating Part

Yes

Ports

1

Stackable

No

Temperature Range - Operating

-40° to +100°C

Electrical

Current - Maximum per Contact

11.0A, 9.0A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

AS-31067-100-001

Packaging Specification

PK-30907-737-001, PK-31301-076-001

Product Specification

PS-31100-0001-001

Sales Drawing

SD-31109-003-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

31067 Series

Mates With

H-DAC 64 3 Way Male Housing Assembly

310671040 , 310671070

Use With

See Product Specification

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION