

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0334724806

Status:

Active

Overview:

MX150 Connector System

Description:

MX150 Mat-Sealed Female Connector Assembly, Dual Row, 8 Circuits, Keying Option A, with Connector Position Assurance, Black



Documents:	
3D Model (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
Drawing (PDF)	Application Specification AS-33611-001-001 (PDF)
3D Model	Datasheet (PDF)
Product Specification PS-33472-000-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33472-100-001 (PDF)	

General	
Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	with Connector Position Assurance (CPA)
Overview	MX150 Connector System
Product Name	MX150
Taxonomy	Connector Housings
UPC	889056886277
Physical	
Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	11.788/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33611-001-001
Product Specification	PS-33472-000-001
Sales Drawing	334720802-001, PK-31300-903-001

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

33472 Series

Mates With

MX150 Male Sealed Connector [33482](#)

MX150 Male Bulkhead Twist-Lock
Sealed Connector [348404410](#)

Use With

MX150 Female Terminal [33012](#) , [33001](#)

MX150 Sealed Cavity Plug [343450001](#)

MX150 Backshell [349510811](#) ,
[349510821](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION