





PCB HOLES
PCB THICKNESS 1.6 mm MAX.
PCB LOCHBILD
PCB DICKE 1.6 mm MAX.



A1	-	REVISIONS							
		ÄNDERUNGEN		DESCRIPTION		DATE	OWN	APVD	
		PROJECT NO.:		BESCHREIBUNG					
		EGLPC01017							
		P	LTR						
		A1		EG0005760		18JUN2001	NG	GF	
		A2		DRAWING ADJUSTED		06DEC2002	NG	GF	

MATERIAL / MATERIAL: PBT, UL-94 V2	7
SHELL MATERIAL / GEHÄUSEMATERIAL: CUZN	
FINISH / BESCHICHTUNG: TRIBOR 4 µm	
CODING / KODIERUNG	6
WIRE GAGE / DRAHTGROSSE IN mm ² : 0.25	5
WIRE GAGE / DRAHTGROSSE IN mm ² : 0.14	4
CONTACT RESISTANCE / KONTAKTWIDERSTAND: => 5 mΩ	3
RATED CURRENT PER CONTACT / NENNSTROM PRO KONTAKT: 3 A	2
RATED CURRENT PER CONTACT / NENNSTROM PRO KONTAKT: 1 A	1
SHELL PROTECTION CLASS / SCHUTZKLASSE: IP 65 / DIN 40050	
TERMINATION: SOLDERING / VERBINDUNG: LOETKONTAKTE	
TEST VOLTAGE / PRUEFSPANNUNG: 500 VAC	
OPERATING VOLTAGE / BETRIEBSSPANNUNG: 60 VAC	
OPERATING TEMPERATURE: -40°C TO +80°C / ARBEITSTEMPERATUR: -40°C BIS +80°C	
MATING CYCLES / STECKZYKLEN: 500 MAX.	
TECHNICAL DATA TECHNISCHE DATEN	

TYCO-NO. / TYCO NR.					
0-1418049-1	0-1418048-1	6-1437719-5	6-1437719-4	6-1437719-3	
1					INSULATION TUBE 8 POS. / ISOLIERHUELSE 8 POL. 12
	1				INSULATION TUBE 7 POS. / ISOLIERHUELSE 7 POL. 11
		1			INSULATION TUBE 5 POS. / ISOLIERHUELSE 5 POL. 10
			1		INSULATION TUBE 4 POS. / ISOLIERHUELSE 4 POL. 9
				1	INSULATION TUBE 3 POS. / ISOLIERHUELSE 3 POL. 8
8	7				MALE PIN APPLIED BY PRESSURE / STIFTKONTAKT EINGEPRESST 7
		5	4	3	MALE PIN APPLIED BY PRESSURE / STIFTKONTAKT EINGEPRESST 6
1	1	1	1	1	NUT / MUTTER 5
1	1	1	1	1	SEAL / DICHTUNG 4
1	1	1	1	1	SEAL / DICHTUNG 3
1	1	1	1	1	HOUSING / GEHAEUSE 2
1	1	1	1	1	GROUND ON PCB SPRING / VERBINDUNGSFEDER ZUR PCB MASSE 1
-	-	-	-	-	REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG REV.)
QTY REQD PER ASSY					
T01-0570-P08	T01-0570-P07	T01-0570-P05	T01-0570-P04	T01-0570-P03	
					DESCRIPTION / BESCHREIBUNG
					ITEM-NO. TEIL-NR.
					PARTS LIST / TEILE LISTE

THIS DRAWING IS UNCLASSIFIED UNTER DEN BEDINGUNGEN DER VERTRÄGE © COPYRIGHT 2000 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED. ALLE RECHTE VORBEHALTEN.		DWN H. GEISLER 18JUN2001		tyco Electronics AMP GmbH 0 - 64625 Bensheim	
DIMENSIONS MASSENHEITEN: (MM)		CHK H. SCHERER 18JUN2001		NAME T01 MALE PLUS CONN. PANEL MNT. PCB VER. 3-8 POS. 180 DGR. T01 STIFTSTECKER.EINBAU. PCB VER. 3-8 POS. 180 GRAD	
TOLERANCES, UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS		APVD G. FELDMEIER 18JUN2001		SIZE 00779	
0 PLC ±0.3 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±		PRODUCT SPEC PRODUKTSPEZ.		DRAWING NO. 6-1437719-3	
APPLICATION SPEC VERARBEITUNGSPEZ.		WEIGHT GEWICHT		RESTRICTED TO NUR FUER	
MATERIAL -		CUSTOMER DRAW ING		KUNDENZEICHNUNG	
SCALE MASSSTAB		SHEET BLATT		1 OF VON 1	
REV A2		REV A2		REV A2	