

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0670688011

Status:


Active

Overview:

USB Connectors: USB Type-A, USB Type-B, and USB Type-C Plugs and Receptacles

Description:

Universal Serial Bus (USB), Shielded I/O, Type B Receptacle, Right-Angle with Straight Tabs, Color Black, 0.76µm Gold (Au) Plating, Tray Pack, Lead-Free



Documents:	
3D Model	Packaging Specification PK-67068-001-001 (PDF)
Drawing (PDF)	Test Summary TS-67068-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-67998-0000-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	I/O Connectors
Series	67068
Application	Wire-to-Board
Comments	Single
Component Type	Receptacle
Overview	USB Connectors: USB Type-A, USB Type-B, and USB Type-C Plugs and Receptacles
Product Name	USB
Standard	USB 2.0
Taxonomy	I/O Connectors
Type	B
UPC	822348721603
Physical	
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Mounting Style	Top-Mount
Net Weight	3.466/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.80mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	0° to +50°C

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

67068 Series

Mates With

USB Type B Plug

Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	1.5A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V (RMS)
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-67068-001-001
Product Specification	PS-67998-0000-001
Sales Drawing	SD-67068-003-001, SD-67068-003-002, SD-67068-003-003, SD-67068-003-004
Test Summary	TS-67068-001-001

This document was generated on 12/05/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION