

T-1 (3mm) SOLID STATE LAMPS

L-934VGC-E GREEN
L-934MGC MEGA GREEN

Features

- •ULTRA BRIGHTNESS.
- •BOTH DIFFUSED AND WATER CLEAR LENS ARE AVAILABLE.
- •OUTSTANDING MATERIAL EFFICIENCY.
- •RELIABLE AND RUGGED.
- •IC COMPATIBLE/LOW CURRENT CAPABILITY.


Description

The Green source color devices are made with DH InGaN on GaAs substrate Light Emitting Diode.

The Mega Green source color devices are made with

DH InGaAIP on GaAs substrate Light Emitting Diode.

Package Dimensions



Notes

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25 (0.01")$ unless otherwise noted.
- 3. Lead spacing is measured where the lead emerge package.
- 4. Specifications are subject to change without notice.

SPEC NO: KDA0301 APPROVED: J.LU REV NO: V.1 CHECKED: DATE: SEP/17/2001

PAGE: 1 OF 4

DRAWN: J.X.FU



Selection Guide

Part No.	Dice	Lens Type	lv (mcd) @ 20 mA		Viewing Angle
			Min.	Тур.	201/2
L-934MGC	MEGA GREEN (InGaAIP)	WATER CLEAR	200	700	50°
L-934VGC-E	GREEN (InGaN)	WATER OLEAR	1500	2000	50°

Note

Electrical / Optical Characteristics at T_A=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions	
λpeak	Peak Wavelength	Mega Green Green	574 518		nm	IF=20mA	
λD	Dominate Wavelength	Mega Green Green	568 525		nm	IF=20mA	
Δλ1/2	Spectral Line Halfwidth	Mega Green Green	26 36		nm	IF=20mA	
С	Capacitance	Mega Green Green	20 50		pF	VF=0V;f=1MHz	
V _F	Forward Voltage	Mega Green Green	2.1 4.0	2.5 4.5	V	IF=20mA	
I _R	Reverse Current	All		10	uA	VR = 5V	

Absolute Maximum Ratings at T_A=25°C

Parameter	Mega Green	Green	Units		
Power dissipation	105	120	mW		
DC Forward Current	30	30	mA		
Peak Forward Current [1]	205	150	mA		
Reverse Voltage	5	5	V		
Operating/Storage Temperature	-40°C To +85°C				
Lead Solder Temperature [2]	260°C For 5 Seconds				

Notes

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 4mm below package base.

SPEC NO: KDA0301 APPROVED: J.LU REV NO: V.1 CHECKED:


DATE: SEP/17/2001

PAGE: 2 OF 4

DRAWN: J.X.FU


^{1.} θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.








RELATIVE INTENSITY Vs. WAVELENGTH

Mega Green L-934MGC












DATE: SEP/17/2001 DRAWN: J.X.FU PAGE: 3 OF 4


Kingbright

Green L-934VGC-E









DATE: SEP/17/2001 DRAWN: J.X.FU PAGE: 4 OF 4