







Circuits	Dimension		Circuits	Dimension	
	A	B		A	B
2	6.7	—	14	24.7	18.0
4	9.7	3.0	16	27.7	21.0
6	12.7	6.0	18	30.7	24.0
8	15.7	9.0	20	33.7	27.0
10	18.7	12.0	22	36.7	30.0
12	21.7	15.0	24	39.7	33.0



Specifications:

Current rating:5.0A AC,DC
Voltage rating:250V AC, DC
Contact tesistance:10m ohm Max
Insulation resistance:1000M ohm Min
Withstanding voltage:AC 1500V AC/minute
Operating Temperature:−25°C ~ +105°C
Materials:
Insulator:High Temp Plastic (Nylon 46 UL94V-0)
Insulator Color:Black
Contact:Copper Alloy
Finish:Tin Plated



TOLERANCE (mm)		APPROVALS		DATE	TITLE 3.0mm Power Connector Top Entry Dip w/Pegs	AMPHENOL Amphenol European Design Center		
X.	±0.3	DRAWN Stephane		06/Jun/2007		Scale N.A.	Sheet 1 of 1	
X.X	±0.2	CHECKED Rob		06/Jun/2007				
X.XX	±0.15	APPROVED Rob		06/Jun/2007				
UNLESS OTHERWISE SPECIFIED:				UNIT : mm		SIZE :		DRAWING N°
					A4	MF30-DVP1-XX		A